

A	The information provided herein is from CONNFELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNFELY or its affiliates. Unauthorized use or modification is strictly prohibited without prior written consent from CONNFELY. All intellectual properties provided herein are for reference purposes only and does not constitute authorization of its use in any format or manner. CONNFELY may enforce its intellectual property rights at its own discretion; failures or delays to exercise such rights does not constitute a waiver of such rights.	Dept	Qty
		DC	1
		ED	1
		IE	1
B	ISO	1	
	PD	1	
	R&D	1	
	SD	1	
C	QA	1	
	QC	1	
	QE	1	
D			
E			
F			
G			
H			

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 10/04/05'		LJC 10/04/05'
B	DRAWING UPDATE	JLZ 08/31/18'		

NOTES:

1. Materials
 - 1.1 Insulator: Thermoplastic (UL 94V-0).
 - 1.2 Contact: Copper alloy.
2. Specification
 - 2.1 Temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$.
 - 2.2 Contact resistance: $20\text{m}\Omega$ max.
 - 2.3 Insulation resistance: $1000\text{M}\Omega$ min.
 - 2.4 Dielectric withstanding voltage: AC 500V per minute.

3. Product number code:



DS1020- X X X X

Contact type
D: Double side

Contact plating
T1: Tin

Mounting type
S: V/T type
R: R/A type

No. of contacts
02~27



(Series Image-Reference Only)

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	FFC/FPC CONNECTOR
X. ±0.60		X. ±5°		UNITS	mm		PITCH 2.54mm LIF.T/H
.X ±0.38		.X ±3°		SHEET SIZE	A4	SERIES	DS1020 SERIES
.XX ±0.25		.XX ±2°		 晨翔电子有限公司 CONFLY CONFLY ELECTRONIC CO. LTD			
DRAWING TYPE		CUSTOMER					
SCALE	1:1	SHEET	1 OF 1				
DRAWING NO.	C-DS1020-XXXX-B						