



Kontaktbuchse 1mm geschlitzt

Einsatzbereich: 623 Stecker, 10polig
923 Stecker, 8- und 9polig
723 htec
740 htec

Best.-Nr.: 60.216.11

Elektrische Werte

*Bemessungsstrom bis 14 A
Durchgangswiderstand < 5 mOhm

Werkstoff

Kontakt Messing, vergoldet

Anschluß


Anschlußart crimp
Anschlußbereich 0,5 - 1,5 mm²
Abisolierlänge 5 mm
Crimpeinstellungen sind individuell zu wählen

Mechanische Werte

Steckzyklen 500

Werkzeuge (nicht im Lieferumfang enthalten)

digitale Crimpzange Best.-Nr.: C0.236.00
analoge Crimpzange Best.-Nr.: C0.201.00
(Positioniereinsatz für 1mm Kontakte Best.-Nr.: C0.252.00)



Hauptabmessungen

Kontaktbuchse





Contact Socket 1mm slotted

application area: 623 plug, 10way
923 plug, 8-und 9way
723 htec
740 htec

order code: 60.216.11

Electrical Data

*nominal current max 14 A
contact resistance < 5 mOhm

Material

contact brass, gold plated

Termination


kind of termination crimp
cross section 0.5 - 1.5 mm²
stripping length 5 mm
crimp settings select individually

Mechanical Data

mating cycles 500

Tools (not included in delivery)

digitale crimping tool order code: C0.236.00
(analog crimping tool order code: C0.201.00
positioning insert for 1mm contacts order code: C0.252.00)



Main Dimensions

contact socket

