


Intelligent Fuse - Automotive Maxi Blade Fuse

AMP-L-Intelligent Maxi Blade Fuse

Intelligent Fuse is designed with an indicating device on top which lights up when the fuse is blown further provide the easy identification for blown fuse that needs replacement inside the fuse box assembly.



Unit : mm

Electrical Characteristics :

TIME CURRENT CHARACTERISTICS			
% of Rating	Current Rating	Opening Time	
		Minimum	Maximum
135%	20 – 60 Amp	60 sec.	1800 sec.
135%	70 – 100 Amp	60 sec.	3600 sec.
200%	20 – 100 Amp	4 sec.	60 sec.
350%	20 – 100 Amp	0.2 sec.	7 sec.

Patented in Taiwan, Japan and U.S.A.

Color – Coding: Blade Fuses are color-coded for easy amperage identification.


Material: Fuse Body is made from insulating plastic.
Fuse Element : Zinc Alloy

Indicating Device: Single patented Bi-Polar SMD LED device rated at 32V DC Maximum.

Ordering Information:

Catalogue Number	Ampere Rating	Voltage Rating	Color Code	Nominal Resistance Cold Ohms
AMP-L020	20	32	Yellow	0.0039
AMP-L030	30	32	Green	0.0024
AMP-L040	40	32	Amber	0.0018
AMP-L050	50	32	Red	0.0014
AMP-L060	60	32	Blue	0.0011
AMP-L070	70	32	Tan	0.0009
AMP-L080	80	32	Nature	0.0008
AMP-L100	100	32	Violet	0.0006

Average Time Current Curves



瀚新科技股份有限公司 Hansor Polymer Technology Corp.

台北縣中和市連城路 222 巷 11 號 2 樓

2F, No. 11, LN.222, Liancheng Rd. Zhonghe Dist. New Taipei City, Taiwan, R.O.C. TEL:886-2-22220101 (REP.) FAX:886-2-22228080

HANSOR PTC