



intercontec
products

Kontaktstift ø1 mm

Einsatzbereich: -alle 623 Isolierkörper

TE Teile Nr.: 61-0006-011-000
IC Ref. Nr.: 61.006.11

Elektrische Daten

Bemessungsstrom max. 10 A*
Durchgangswiderstand < 5 mOhm

Werkstoffe


Kontakt Messing, vergoldet

Anschluss

Anschlussart lötlöt
Anschlussbereich 1,0 - 1,5 mm²
Abisolierlänge 5 mm

Mechanische Werte

Steckzyklen 500



Hauptabmessungen

Kontaktstift

Y6-B538-000-0DE erstellt: 01.12.2009/FM; geändert: 25.06.2018/JA

© 2018 TE Connectivity.

TE Connectivity, TE connectivity (logo), intercontec (logo) und speedtec sind Marken.

Auch wenn TE Connectivity (TE) bemüht ist, die Korrektheit der Informationen in diesem Beitrag sicherzustellen, übernimmt TE keinerlei Gewährleistung dafür, dass diese fehlerfrei, zutreffend, korrekt, verlässlich oder aktuell sind. TE behält sich das Recht vor, die in diesem Beitrag genannten Informationen jederzeit ohne Ankündigung zu ändern. TE weist ausdrücklich jegliche Gewährleistung hinsichtlich der in diesem Beitrag genannten Informationen zurück, einschließlich der implizierten Gewährleistung der Marktgängigkeit oder Eignung für bestimmte Zwecke. Die Maßangaben in diesem Beitrag dienen ausschließlich zu Referenzzwecken und Änderungen sind vorbehalten. Änderungen der Spezifikationen sind vorbehalten. Bitte fragen Sie TE nach den aktuellen Maßangaben und Designspezifikationen

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* Bei max. Anschlussquerschnitt



intercontec
products

Contact Pin $\varnothing 1$ mm

for: -all 623 Insulation Insert

TE part number: 61-0006-011-000

IC reference number: 61.006.11

Technical Data

rated current max. 10 A*
contact resistance < 5 mOhm

Material


contact brass, gold plated

Termination

kind of termination solder
cross section 1.0 - 1.5 mm²
stripping length 5 mm

Mechanical Data

mating cycles 500



Main Dimensions

contact pin

Y6-B538-000-0EN issued: 19.03.2015/MH; modified: 25.06.2018/JA

© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH
Bernrieder Straße 15
94559 Niederwinkling, Germany
+49 9962 2002 - 0
intercontec@te.com
www.intercontec.biz



* for max. wire cross-section