

SCHLEGEL®
ELEKTROKONTAKT


EC Declaration of Conformity

Product /Type designation	European Directives and used standards					
	Mach				EMC	
	2006/42/EC of 17.05.2006	DIN EN 60947-5-5: 2017-08 *)	EN ISO 13850:2015)	DIN EN 60204-1: 2010 *)	2014/30/EU of 26.02.2014	IEC 62026-2: 2019 *)
Contacts connected to emergency stops: AZOSOI(_AU), AZSOSO(_AU), BZ(L)O(5)(K)(_AU); AT(_AU), AZ011(_AU), AZ00(_AU), AZ(L)2(_AU), AZOSOI(_AU), AZSOSO(_AU), AZ2N(_AU), AZ(L)4O(_AU); BZ(L)OO(5)(K)(_AU), BZ(L)OI(5)(K)(_AU), BZ(L)OS(5)(K)(_AU), BZ(L)O(5)(K)(_AU); DST(O)(OSDE)(I), DMSTOSF,DT(O)(I), DMTOSF(A), DMR, DSAL; MT(O)(I)(SF)(SFE)(ON)(IV)(97)(Z)(_545); MHT(O)(OO)(IOO)(OSF)(OSFO)(OSFI)(OSFOI)(OSFOIL)(_545) (OSFE)(OSFEO)(OSFEOO)(OSFEOI); MZ(TI)(TO); MAL; MHR_3; MHR_5; MTZU(_564); ETR; PTOO(_AU), PTPOO(_AU), PTPOI(_AU), PTFOO(_AU); PTFOI(_AU), PTFPOI(_AU), PTFPOO(_AU); PTS(L)(OOO)(OOI)(OO)(OI)(O)(_AU); FRT(F)(P)(L)(OOI)(OO)(OI)(3O)(S)(O)(_AU); PTSFP(L)(OOO)(OOI)(OO)(OI)(O)(_AU); FRT(F)(P)(L)(OOI)(OO)(OI)(3O)(O)(S)(_AU);	•	•	•	•		
ASI_SAW(16)(22)(A)(E)	•	•	•	•	•	•
SILH_ASI(E)(A)_QR(B)(SK)(L)UV(SE)(P)	•	•	•	•	•	•
SIL_QR(B)(SK)(L)UV(SE)(P)(O)(OI)(OO)(OOI)(OSF)(_M12); MB(M)(P_)(W_)(124_)(125_)(128_)(GR_)FRVK (L) (O) (OO (OI) (OOI) (OOO) (_AU) (NOOITI) (NOOM) (NOOTLI) (NOOOTI) (NOITI) (NOII) (NOOTI) (NOOTII) (NLOOTI) (NOOOM) (NLOITI) (NLOIM) (NOOIM)	•	•	•	•		
SVAB_123064_01, SVAB_123064_01, SVAB_125375_001	•	•	•			
SVA40_126084_01, SVA40_121851_02; S41_01, S42_02, S43_03, S44_04, S45_05, S46_06, S43_07, S42_08, S44_09, S45_10, S46_11	•	•	•	•		
SIL(H)(16)(22)/1, MB(M)(P_)(W_)(124_)(125_)(128_)(GB)(GB2)_LEER	•			•		
RSK22, RRSK, RSKF22, RKSK	•	•	•			

*) In case of amendments, the referenced standard is EN CCCCC:YYYY, its previous amendments, if any, and the new, quoted amendment.

Dürmentingen, 12.09.2022

(Place, date)


(Managing Director)

EG-Konformitätserklärung

Produkt / Typenbezeichnungen	Richtlinie und angewandte Normen					
	Masch				EMV	
	2006/42/EG vom 17.05.2006	DIN EN 60947-5-5: 2017-08 *)	EN ISO 13850:2015)	DIN EN 60204-1: 2018	2014/30/EU vom 26.02.2014	IEC 62026-2: 2019 *)
Kontakte in Verbindung mit Not-Halt: AZOSOI(_AU), AZSOSO(_AU), BZ(L)O(5)(K)(_AU); AT(_AU), AZ011(_AU), AZ00(_AU), AZ(L)2(_AU), AZOSOI(_AU), AZSOSO(_AU), AZ2N(_AU), AZ(L)4O(_AU); BZ(L)OO(5)(K)(_AU), BZ(L)OI(5)(K)(_AU), BZ(L)OS(5)(K)(_AU), BZ(L)O(5)(K)(_AU); DST(O)(OSDE)(I), DMSTOSF,DT(O)(I), DMTOSF(A), DMR, DSAL; MT(O)(I)(SF)(SFE)(ON)(IV)(97)(Z)(_545); MHT(O)(OO)(IOO)(OSF)(OSFO)(OSFI)(OSFOI)(OSFOIL)(_545) (OSFE)(OSFEO)(OSFEOO)(OSFEOI); MZ(TI)(TO); MAL; MHR_3; MHR_5; MTZU(_564); ETR; PTOO(_AU), PTPOO(_AU), PTPOI(_AU), PTFOO(_AU); PTFOI(_AU), PTFPOI(_AU), PTFPOO(_AU); PTS(L)(OOO)(OOI)(OO)(OI)(_AU), PTSFP(L)(OOO)(OOI)(OO)(OI)(O)(_AU); FRT(F)(P)(L) (OOI)(OO)(OI)(3O)(O)(S)(_AU);	•	•	•	•		
ASI_SAW(16)(22)(A)(E)	•	•	•	•	•	•
SILH_ASI(E)(A)_QR(B)(SK)(L)UV(SE)(P)	•	•	•	•	•	•
SIL_QR(B)(SK)(L)(U)V(SE)(P)(O)(OI)(OO)(OOI)(OSF)(_M12); MB(M)(P_)(W_)(124_)(125_)(128_)(GR)_FRVK (L) (O) (OO) (OI) (OOI) (OOO) (_AU) (NOOITI) (NOOM) (NOOTLI) (NOOOTI) (NOITI) (NOII) (NOOTI) (NOOTII) (NLOOTI) (NOOOM) (NLOITI) (NLOIM) (NOOIM)	•	•	•	•		
SVAB_123064_01, SVAB_123064_01, SVAB_125375_001	•	•	•			
SVA40_126084_01, SVA40_121851_02; S41_01, S42_02, S43_03, S44_04, S45_05, S46_06, S43_07, S42_08, S44_09, S45_10, S46_11	•	•	•	•		
SIL(H)(16)(22)/1, MB(M)(P_)(W_)(124_)(125_)(128_)(GB)(GB2)_LEER	•			•		
RSK22, RRSK, RSKF22, RSKK	•	•	•			

*) Bei Änderungen setzt sich die betroffene Norm aus EN CCCCC:YYYY, ihren vorangegangenen Änderungen, falls vorhanden, und der zitierten neuen Änderung zusammen.

Dürmentingen, 12.09.2022

(Ort, Datum)


(Geschäftsführer)