




HY20A05FSE37AP0

Air performance



Single wires AWG30, tinned
VCC = red GND = black FG = black
No obstruction within 1mm of air intake

Certifications	CE / WEEE
U [V DC]	5 [V]
I _{typ} [mA]	20 [mA]
I _{max} [mA]	80 [mA]
V _{max} [m³/h]	0,15 [m³/h]
P _{max} [Pa]	5,8 [Pa]
Noise [dB(A)]	4 [dB(A)]
Rotation Speed [min ⁻¹]	6400 [min ⁻¹]
Signal / FG [Imp/U]	3 [Imp/U]
PWM	no
Temp. [°C]	-40 [°C] - 80 [°C]
L10/MTTF @ 40°C [h]	40000 [h] - 210000 [h]
Bearing type	MagFix
Weight [kg]	0,003

* Noise and rotation speed are subject to deviations due to tolerance.

ORDER INFORMATION

HY20A05FSE37AP0 113231006

Technical changes without notice
06.06.2024


SEPA EUROPE GmbH DE-79427 Eschbach Tel.: +49 7634/59459-0 info@sepa-europe.com



HY20A05FSE37AP0

FG

IMPORTANT: The pulse output is not protected against short circuit and must not be connected to GND or VCC without series resistor. A pull-up-resistor is needed. Insulate not used pulse output!



Run: Low=0.3Vmax High=VCC
Stop: Low or High
 $T = \text{rpm} / 60 \cdot [\text{pulses per revolution}]$