



Date	SYM	REVISION RECORD	AUTH	DR.	CK.
12/01/17	A	UPDATED SPECIFICATION	T.B.	B.S.	
04/12/19	B	UPDATED TO "ROHS COMPLIANT"	T.B.	B.S.	
11/26/19	C	WAS RATED 30AMP. ADDED WIRE LENGTH	T.B.	B.S.	
11/17/21	D	WAS 14 AWG	T.B.	B.S.	



NOTES:

1. MATERIAL:

HOUSING : NYLON 6, UL 94-V2, UL FILE NO. E36632

2. LEAD WIRE IN LOOP: 8" OVERALL LENGTH RED WIRE, 16 AWG, UL-1015, 600V, 105°C, FLAME RATING VW-1, UL FILE NO. E77961, OR ENGINEERING APPROVED EQUIVALENT

3. RATED CURRENT: 20A

4. ACCEPTS AGC/JMC FUSES

5. INSULATION RESISTANCE AT 500V DC: 100MΩ MIN

6. CONTACT RESISTANCE: 5mΩ AT 1A DC

7. DIELECTRIC STRENGTH FOR 60 SECONDS: AC 1500V MIN ROHS COMPLIANT

Tolerance (Except as noted)	Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal $\pm .5$ (.020)		Scale	Drawn By B.S.
			Approved By T.B.
Fractional $\pm .8$ (.030)	Title INLINE FUSE HOLDER		
Angular $\pm 3^\circ$	Date 11/26/19	Drawing Number BF309	