

SAFETY DATA SHEET

This safety data sheet was created pursuant to the requirements of:
Regulation (EC) No. 1907/2006 and Regulation (EC) No. 1272/2008

CYA-Test Photometer

Revision date 06-10-2024

Revision Number 1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Code(s) TBSPCAT
Product Name CYA-Test Photometer
Unique Formula Identifier (UFI) QKDT-0H5V-C810-GN06
Pure substance/mixture Mixture
Contains Melamine

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Reagent for water analysis
Uses advised against Others

1.3. Details of the supplier of the safety data sheet

Manufacturer

Water-i.d. GmbH
Daimlerstr. 20
76344 Eggenstein, Germany
Tel.: +49 (0) 721 78 20 29 0, Fax: +49 (0) 721 78 20 29 11
Website: www.water-id.com
EHS / Compliance: lab@water-id.com

1.4. Emergency telephone number

Emergency Telephone

United Kingdom	+44 1235 239670 English
----------------	----------------------------

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Regulation (EC) No 1272/2008

Acute toxicity - Dermal	Category 4 - (H312)
Carcinogenicity	Category 2 - (H351)
Specific target organ toxicity — repeated exposure	Category 2 - (H373)

2.2. Label elements

Contains Melamine



Signal word
Warning

Hazard statements

H312 - Harmful in contact with skin

H351 - Suspected of causing cancer

H373 - May cause damage to organs through prolonged or repeated exposure

Precautionary Statements - EU (§28, 1272/2008)

P302 + P352 - IF ON SKIN: Wash with plenty of water and soap

P321 - Specific treatment (see supplemental first aid instructions on this label)

P501 - Dispose of contents/ container to an approved waste disposal plant

P362 + P364 - Take off contaminated clothing and wash it before reuse

P260 - Do not breathe dust/fume/gas/mist/vapours/spray

P314 - Get medical advice/attention if you feel unwell

Additional information

This product requires tactile warnings if supplied to the general public.

2.3. Other hazards

No information available.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

Chemical name	Weight-%	REACH registration number	EC No (EU Index No)	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	M-Factor	M-Factor (long-term)
Melamine 108-78-1	5-10	No data available	203-615-4	Carc. 2 (H351) STOT RE 2 (H373)			
Polyethylene glycol 25322-68-3	1-10	No data available	-	No data available			
Citric Acid 77-92-9	1-10	No data available	201-069-1	Eye Irrit. 2 (H319) STOT SE 3 (H335)			
Silica, amorphous 7631-86-9	<1	No data available	231-545-4	No data available			

Full text of H- and EUH-phrases: see section 16

Acute Toxicity Estimate

If LD50/LC50 data is not available or does not correspond to the classification category, then the appropriate conversion value from CLP Annex I, Table 3.1.2, is used to calculate the acute toxicity estimate (ATE_{mix}) for classifying a mixture based on its components

Chemical name	Oral LD50 mg/kg	Dermal LD50 mg/kg	Inhalation LC50 - 4 hour - dust/mist - mg/L	Inhalation LC50 - 4 hour - vapour - mg/L	Inhalation LC50 - 4 hour - gas - ppm
Melamine	3161	1000			

Chemical name	Oral LD50 mg/kg	Dermal LD50 mg/kg	Inhalation LC50 - 4 hour - dust/mist - mg/L	Inhalation LC50 - 4 hour - vapour - mg/L	Inhalation LC50 - 4 hour - gas - ppm
108-78-1					
Polyethylene glycol 25322-68-3	22000	20000			
Citric Acid 77-92-9	3000	2000			
Silica, amorphous 7631-86-9	7900	5000	58.8		

This product contains one or more candidate substance(s) of very high concern (Regulation (EC) No. 1907/2006 (REACH), Article 59)

Chemical name	CAS No.	SVHC candidates
Melamine	108-78-1	

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	Show this safety data sheet to the doctor in attendance.
Inhalation	Remove to fresh air.
Eye contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Keep eye wide open while rinsing. Do not rub affected area. Get medical attention if irritation develops and persists.
Skin contact	Wash off immediately with plenty of water for at least 15 minutes. If symptoms persist, call a doctor.
Ingestion	Do NOT induce vomiting. Rinse mouth. Never give anything by mouth to an unconscious person. Call a doctor.
Self-protection of the first aider	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination. Wear personal protective clothing (see section 8). Avoid contact with skin, eyes or clothing.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms	May cause redness and tearing of the eyes. Burning sensation.
-----------------	---

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors	Treat symptomatically.
------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Large Fire	CAUTION: Use of water spray when fighting fire may be inefficient.
Unsuitable extinguishing media	Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical	No information available.
---	---------------------------

5.3. Advice for firefighters

Special protective equipment and precautions for fire-fighters	Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.
---	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Use personal protective equipment as required.
Other information	Refer to protective measures listed in Sections 7 and 8.
For emergency responders	Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions	Prevent further leakage or spillage if safe to do so.
----------------------------------	---

6.3. Methods and material for containment and cleaning up

Methods for containment	Prevent further leakage or spillage if safe to do so.
Methods for cleaning up	Take up mechanically, placing in appropriate containers for disposal.
Prevention of secondary hazards	Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sections	See section 8 for more information. See section 13 for more information.
------------------------------------	--

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling	Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Do not eat, drink or smoke when using this product.
General hygiene considerations	Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions	Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up.
---------------------------	---

7.3. Specific end use(s)

Risk Management Methods (RMM)	The information required is contained in this Safety Data Sheet.
--------------------------------------	--

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits

Chemical name	European Union	Austria	Belgium	Bulgaria	Croatia
Polyethylene glycol 25322-68-3	-	TWA: 1000 mg/m ³ STEL 4000 mg/m ³	-	-	-
Silica, amorphous 7631-86-9	TWA: 0.1 mg/m ³	TWA: 4 mg/m ³	-	TWA: 0.1 mg/m ³	-
Chemical name	Cyprus	Czech Republic	Denmark	Estonia	Finland
Polyethylene glycol 25322-68-3	-	-	TWA: 1000 mg/m ³	-	-
Citric Acid 77-92-9	-	TWA: 4 mg/m ³	-	-	-
Silica, amorphous 7631-86-9	-	TWA: 0.1 mg/m ³ TWA: 4.0 mg/m ³	TWA: 1.5 mg/m ³ TWA: 0.1 mg/m ³	TWA: 2 mg/m ³	TWA: 5 mg/m ³
Chemical name	France	Germany TRGS	Germany DFG	Greece	Hungary
Polyethylene glycol 25322-68-3	-	TWA: 200 mg/m ³	TWA: 250 mg/m ³ Peak: 500 mg/m ³	-	-
Citric Acid 77-92-9	-	TWA: 2 mg/m ³	TWA: 2 mg/m ³ Peak: 4 mg/m ³	-	-
Silica, amorphous 7631-86-9	-	TWA: 4 mg/m ³	TWA: 0.02 mg/m ³ Peak: 0.16 mg/m ³	TWA: 0.1 mg/m ³	-
Chemical name	Ireland	Italy MDLPS	Italy AIDII	Latvia	Lithuania
Silica, amorphous 7631-86-9	TWA: 6 mg/m ³ TWA: 2.4 mg/m ³ STEL: 18 mg/m ³ STEL: 7.2 mg/m ³	TWA: 0.1 mg/m ³	-	TWA: 1 mg/m ³	-
Chemical name	Luxembourg	Malta	Netherlands	Norway	Poland
Silica, amorphous 7631-86-9	-	-	TWA: 0.075 mg/m ³	STEL: 3 mg/m ³	TWA: 10 mg/m ³ TWA: 2 mg/m ³
Chemical name	Portugal	Romania	Slovakia	Slovenia	Spain
Polyethylene glycol 25322-68-3	-	-	TWA: 1000 mg/m ³	TWA: 1000 mg/m ³ STEL: STEL mg/m ³	-
Silica, amorphous 7631-86-9	TWA: 0.05 mg/m ³	-	-	TWA: 4 mg/m ³	-
Chemical name	Sweden		Switzerland		United Kingdom
Polyethylene glycol 25322-68-3	-		TWA: 500 mg/m ³		-
Citric Acid 77-92-9	-		TWA: 2 mg/m ³ STEL: 4 mg/m ³		-
Silica, amorphous 7631-86-9	-		TWA: 4 mg/m ³		TWA: 6 mg/m ³ TWA: 2.4 mg/m ³ STEL: 18 mg/m ³ STEL: 7.2 mg/m ³

Biological occupational exposure limits

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Derived No Effect Level (DNEL) No information available.

Predicted No Effect Concentration (PNEC)

8.2. Exposure controls**Personal protective equipment**

Eye/face protection Wear safety glasses with side shields (or goggles).

Hand protection Wear suitable gloves.

Skin and body protection Wear suitable protective clothing. Long sleeved clothing.

Respiratory protection	No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.
General hygiene considerations	Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product.
Environmental exposure controls	No information available.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	Solid
Appearance	tablet
Colour	white
Odour	Odourless.
Odour threshold	No data available

Property	Values	Remarks • Method
Melting point / freezing point	No data available	None known
Boiling point / boiling range	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Flash point	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature		None known
pH	6.3	None known
pH (as aqueous solution)	No data available	No information available
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Water solubility	No data available	None known
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Vapour pressure	No data available	None known
Relative density	No data available	None known
Bulk density	No data available	
Liquid Density	No data available	
Relative vapour density	No data available	None known
Particle characteristics		
Particle Size		
Particle Size Distribution		

9.2. Other information

9.2.1. Information with regards to physical hazard classes
Not applicable

9.2.2. Other safety characteristics

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

10.5. Incompatible materials

Incompatible materials None known based on information supplied.

10.6. Hazardous decomposition products

Hazardous decomposition products None known based on information supplied.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure

Product Information

Inhalation	Specific test data for the substance or mixture is not available. May cause irritation of respiratory tract.
Eye contact	Specific test data for the substance or mixture is not available. Causes serious eye irritation. (based on components). May cause redness, itching, and pain.
Skin contact	Specific test data for the substance or mixture is not available. May cause irritation. Prolonged contact may cause redness and irritation. May be absorbed through the skin in harmful amounts. Harmful in contact with skin. (based on components).
Ingestion	Specific test data for the substance or mixture is not available. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhoea.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms May cause redness and tearing of the eyes.

Numerical measures of toxicity

Acute toxicity

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 2,818.50 mg/kg

ATEmix (dermal) 1,540.30 mg/kg

Unknown acute toxicity

13.79 % of the mixture consists of ingredient(s) of unknown acute oral toxicity.

89.79 % of the mixture consists of ingredient(s) of unknown acute dermal toxicity.

99.93 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (gas).

99.93 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (vapour).

99.93 % of the mixture consists of ingredient(s) of unknown acute inhalation toxicity (dust/mist).

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Melamine	= 3161 mg/kg (Rat)	> 1 g/kg (Rabbit)	> 5.19 g/m ³ (Rat) 4 h
Polyethylene glycol	= 22 g/kg (Rat)	> 20 g/kg (Rabbit)	
Citric Acid	= 3 g/kg (Rat)	> 2000 mg/kg (Rat)	
Silica, amorphous	= 7900 mg/kg (Rat)	> 5000 mg/kg (Rabbit)	> 58.8 mg/L (Rat) 4 h

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	May cause skin irritation.
Serious eye damage/eye irritation	Classification based on data available for ingredients. Causes eye irritation.
Respiratory or skin sensitisation	No information available.
Germ cell mutagenicity	No information available.
Carcinogenicity	No information available.

Chemical name	European Union
Melamine	Carc. 2

Reproductive toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Aspiration hazard	No information available.

11.2. Information on other hazards**11.2.1. Endocrine disrupting properties**

Endocrine disrupting properties

11.2.2. Other information

Other adverse effects

SECTION 12: Ecological information**12.1. Toxicity**

Ecotoxicity

Unknown aquatic toxicity Contains 0 % of components with unknown hazards to the aquatic environment.

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Melamine	EC50: =940mg/L (96h, <i>Scenedesmus pannonicus</i>)	LC50: >3000mg/L (96h, <i>Poecilia reticulata</i>)	-	EC50: >2000mg/L (48h, <i>Daphnia magna</i>)
Citric Acid	-	LC50: =1516mg/L (96h, <i>Lepomis macrochirus</i>)	-	-
Silica, amorphous	EC50: =440mg/L (72h, <i>Pseudokirchneriella subcapitata</i>)	LC50: =5000mg/L (96h, <i>Brachydanio rerio</i>)	-	EC50: =7600mg/L (48h, <i>Ceriodaphnia dubia</i>)

12.2. Persistence and degradability**Persistence and degradability****12.3. Bioaccumulative potential**

Bioaccumulation There is no data for this product.

Component Information

Chemical name	Partition coefficient
Melamine	-1.22
Citric Acid	-1.72

12.4. Mobility in soil**Mobility in soil****12.5. Results of PBT and vPvB assessment****PBT and vPvB assessment**

Chemical name	PBT and vPvB assessment
Polyethylene glycol	The substance is not PBT / vPvB
Citric Acid	The substance is not PBT / vPvB
Silica, amorphous	The substance is not PBT / vPvB PBT assessment does not apply

12.6. Endocrine disrupting properties**Endocrine disrupting properties****12.7. Other adverse effects**

No information available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Waste from residues/unused products Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.

Contaminated packaging Do not reuse empty containers.

SECTION 14: Transport information**IATA**

14.1 UN number or ID number Not regulated

14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

IMDG

14.1 UN number or ID number	Not regulated
14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Marine pollutant	Not applicable
14.6 Special precautions for user	
Special Provisions	None
14.7 Maritime transport in bulk according to IMO instruments	

RID

14.1 UN number or ID number	Not regulated
14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

ADR

14.1 UN number or ID number	Not regulated
14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****National regulations****France****Occupational Illnesses (R-463-3, France)**

Chemical name	French RG number	Title
Silica, amorphous 7631-86-9	RG 25	-

Water hazard class (WGK) slightly hazardous to water (WGK 1)

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Authorisations and/or restrictions on use:

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV) This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII)

Persistent Organic Pollutants

Not applicable

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

Chemical name	Biocidal Products Regulation (EU) No 528/2012 (BPR)
Citric Acid - 77-92-9	Product-type 1: Human hygiene

International Inventories

TSCA	Complies
DSL/NDSL	Does not comply
EINECS/ELINCS	Does not comply
ENCS	Complies
IECSC	Complies
KECL	Does not comply
PICCS	Complies
AICS	Complies

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AICS - Australian Inventory of Chemical Substances

15.2. Chemical safety assessment**Chemical Safety Report****SECTION 16: Other information****Key or legend to abbreviations and acronyms used in the safety data sheet****Full text of H-Statements referred to under section 3**

H335 - May cause respiratory irritation

H351 - Suspected of causing cancer

H373 - May cause damage to organs through prolonged or repeated exposure

Legend

SVHC: Substances of Very High Concern for Authorisation:

Legend Section 8: Exposure controls/personal protection

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation

Classification procedure	
Classification according to Regulation (EC) No. 1272/2008 [CLP]	Method Used
Acute oral toxicity	Calculation method
Acute dermal toxicity	Calculation method
Acute inhalation toxicity - gas	Calculation method
Acute inhalation toxicity - Vapour	Calculation method
Acute inhalation toxicity - dust/mist	Calculation method
Skin corrosion/irritation	Calculation method
Serious eye damage/eye irritation	Calculation method
Respiratory sensitisation	Calculation method

Skin sensitisation	Calculation method
Mutagenicity	Calculation method
Carcinogenicity	Calculation method
Reproductive toxicity	Calculation method
STOT - single exposure	Calculation method
STOT - repeated exposure	Calculation method
Acute aquatic toxicity	Calculation method
Chronic aquatic toxicity	Calculation method
Aspiration hazard	Calculation method

Key literature references and sources for data used to compile the SDS

Agency for Toxic Substances and Disease Registry (ATSDR)
 U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 EPA (Environmental Protection Agency)
 Acute Exposure Guideline Level(s) (AEGL(s))
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
 U.S. Environmental Protection Agency High Production Volume Chemicals
 Food Research Journal
 Hazardous Substance Database
 International Uniform Chemical Information Database (IUCLID)
 Japan GHS Classification
 Australian National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
 NIOSH (National Institute for Occupational Safety and Health)
 National Library of Medicine's ChemID Plus (NLM CIP)
 National Library of Medicine's PubMed database (NLM PUBMED)
 National Toxicology Program (NTP)
 New Zealand's Chemical Classification and Information Database (CCID)
 Organisation for Economic Co-operation and Development Environment, Health, and Safety Publications
 Organisation for Economic Co-operation and Development High Production Volume Chemicals Programme
 Organisation for Economic Co-operation and Development Screening Information Data Set
 World Health Organization

Revision date 06-10-2024

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet