

SAFETY DATA SHEET

This safety data sheet was created pursuant to the requirements of:
Regulation (EC) No. 1907/2006 and Regulation (EC) No. 1272/2008

Phenol Red Photometer

Revision date 06-10-2024

Revision Number 1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Code(s) TBSPPH

Product Name Phenol Red Photometer

Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Reagent for water analysis

Uses advised against Others

1.3. Details of the supplier of the safety data sheet

Manufacturer

Water-i.d. GmbH
Daimlerstr. 20
76344 Eggenstein, Germany
Tel.: +49 (0) 721 78 20 29 0, Fax: +49 (0) 721 78 20 29 11
Website: www.water-id.com
EHS / Compliance: lab@water-id.com

1.4. Emergency telephone number

Emergency Telephone

United Kingdom	+44 1235 239670 English
----------------	----------------------------

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Regulation (EC) No 1272/2008

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

2.2. Label elements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

Hazard statements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

2.3. Other hazards

No information available.

SECTION 3: Composition/information on ingredients**3.1 Substances**

Not applicable

3.2 Mixtures

Full text of H- and EUH-phrases: see section 16

Acute Toxicity Estimate

If LD50/LC50 data is not available or does not correspond to the classification category, then the appropriate conversion value from CLP Annex I, Table 3.1.2, is used to calculate the acute toxicity estimate (ATEmix) for classifying a mixture based on its components

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures**4.1. Description of first aid measures**

Inhalation	Remove to fresh air.
Eye contact	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a doctor.
Skin contact	Wash skin with soap and water. In the case of skin irritation or allergic reactions see a doctor.
Ingestion	Rinse mouth.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms	No information available.
----------	---------------------------

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors	Treat symptomatically.
-----------------	------------------------

SECTION 5: Firefighting measures**5.1. Extinguishing media**

Suitable Extinguishing Media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Large Fire	CAUTION: Use of water spray when fighting fire may be inefficient.
Unsuitable extinguishing media	Do not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical	No information available.
--	---------------------------

5.3. Advice for firefighters

Special protective equipment and	Firefighters should wear self-contained breathing apparatus and full firefighting turnout
----------------------------------	---

precautions for fire-fighters gear. Use personal protection equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Ensure adequate ventilation.

For emergency responders Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Take up mechanically, placing in appropriate containers for disposal.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sections See section 8 for more information. See section 13 for more information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling Ensure adequate ventilation.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep container tightly closed in a dry and well-ventilated place.

7.3. Specific end use(s)

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits

Biological occupational exposure limits

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Derived No Effect Level (DNEL) No information available.
Predicted No Effect Concentration

(PNEC)

8.2. Exposure controls**Personal protective equipment**

Eye/face protection No special protective equipment required.

Skin and body protection No special protective equipment required.

Respiratory protection No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

General hygiene considerations Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state Solid
Appearance tablet
Colour orange
Odour Odourless.
Odour threshold

Property	Values	Remarks • Method
Melting point / freezing point	No data available	None known
Boiling point / boiling range	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Flash point	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature		None known
pH	No data available	None known
pH (as aqueous solution)	No data available	No information available
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	None known
Water solubility	No data available	None known
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Vapour pressure	No data available	None known
Relative density	No data available	None known
Bulk density	No data available	
Liquid Density	No data available	
Relative vapour density	No data available	None known
Particle characteristics		
Particle Size		
Particle Size Distribution		

9.2. Other information**9.2.1. Information with regards to physical hazard classes**

Not applicable

*9.2.2. Other safety characteristics***SECTION 10: Stability and reactivity****10.1. Reactivity**

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

10.5. Incompatible materials

Incompatible materials None known based on information supplied.

10.6. Hazardous decomposition products

Hazardous decomposition products None known based on information supplied.

SECTION 11: Toxicological information**11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008****Information on likely routes of exposure****Product Information**

Inhalation Specific test data for the substance or mixture is not available.

Eye contact Specific test data for the substance or mixture is not available.

Skin contact Specific test data for the substance or mixture is not available.

Ingestion Specific test data for the substance or mixture is not available.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Numerical measures of toxicity**Acute toxicity**

The following values are calculated based on chapter 3.1 of the GHS document

ATEmix (oral) 3,065.80 mg/kg

Component Information**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

Skin corrosion/irritation No information available.

Serious eye damage/eye irritation No information available.

Respiratory or skin sensitisation No information available.

Germ cell mutagenicity No information available.

Carcinogenicity No information available.

Reproductive toxicity No information available.

STOT - single exposure No information available.

STOT - repeated exposure No information available.

Aspiration hazard No information available.

11.2. Information on other hazards**11.2.1. Endocrine disrupting properties**

Endocrine disrupting properties

11.2.2. Other information

Other adverse effects

SECTION 12: Ecological information**12.1. Toxicity**

Ecotoxicity

Unknown aquatic toxicity Contains 0 % of components with unknown hazards to the aquatic environment.

12.2. Persistence and degradability

Persistence and degradability

12.3. Bioaccumulative potential

Bioaccumulation No information available.

12.4. Mobility in soil

Mobility in soil

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment

12.6. Endocrine disrupting properties

Endocrine disrupting properties

12.7. Other adverse effects

No information available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Waste from residues/unused products	Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.
Contaminated packaging	Do not reuse empty containers.

SECTION 14: Transport information**IATA**

14.1 UN number or ID number	Not regulated
14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

IMDG

14.1 UN number or ID number	Not regulated
14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Marine pollutant	Not applicable
14.6 Special precautions for user	
Special Provisions	None
14.7 Maritime transport in bulk according to IMO instruments	

RID

14.1 UN number or ID number	Not regulated
14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

ADR

14.1 UN number or ID number	Not regulated
14.2	
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	

Special Provisions

None

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****National regulations****France**

Occupational Illnesses (R-463-3, France)

Germany

Water hazard class (WGK) slightly hazardous to water (WGK 1)

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Authorisations and/or restrictions on use:

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV) This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII)

Persistent Organic Pollutants

Not applicable

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

EU - Plant Protection Products (1107/2009/EC)**Biocidal Products Regulation (EU) No 528/2012 (BPR)****International Inventories**

TSCA	Complies
DSL/NDSL	Does not comply
EINECS/ELINCS	Does not comply
ENCS	Does not comply
IECSC	Complies
KECL	Does not comply
PICCS	Does not comply
AICS	Does not comply

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AICS - Australian Inventory of Chemical Substances

15.2. Chemical safety assessment**Chemical Safety Report**

SECTION 16: Other information**Key or legend to abbreviations and acronyms used in the safety data sheet****Legend**

SVHC: Substances of Very High Concern for Authorisation:

Legend Section 8: Exposure controls/personal protection

TWA TWA (time-weighted average) STEL STEL (Short Term Exposure Limit)
 Ceiling Maximum limit value * Skin designation

Classification procedure	
Classification according to Regulation (EC) No. 1272/2008 [CLP]	Method Used
Acute oral toxicity	Calculation method
Acute dermal toxicity	Calculation method
Acute inhalation toxicity - gas	Calculation method
Acute inhalation toxicity - Vapour	Calculation method
Acute inhalation toxicity - dust/mist	Calculation method
Skin corrosion/irritation	Calculation method
Serious eye damage/eye irritation	Calculation method
Respiratory sensitisation	Calculation method
Skin sensitisation	Calculation method
Mutagenicity	Calculation method
Carcinogenicity	Calculation method
Reproductive toxicity	Calculation method
STOT - single exposure	Calculation method
STOT - repeated exposure	Calculation method
Acute aquatic toxicity	Calculation method
Chronic aquatic toxicity	Calculation method
Aspiration hazard	Calculation method
Ozone	Calculation method

Key literature references and sources for data used to compile the SDS

Agency for Toxic Substances and Disease Registry (ATSDR)
 U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 EPA (Environmental Protection Agency)
 Acute Exposure Guideline Level(s) (AEGl(s))
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
 U.S. Environmental Protection Agency High Production Volume Chemicals
 Food Research Journal
 Hazardous Substance Database
 International Uniform Chemical Information Database (IUCLID)
 Japan GHS Classification
 Australian National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
 NIOSH (National Institute for Occupational Safety and Health)
 National Library of Medicine's ChemID Plus (NLM CIP)
 National Library of Medicine's PubMed database (NLM PUBMED)
 National Toxicology Program (NTP)
 New Zealand's Chemical Classification and Information Database (CCID)
 Organisation for Economic Co-operation and Development Environment, Health, and Safety Publications
 Organisation for Economic Co-operation and Development High Production Volume Chemicals Programme
 Organisation for Economic Co-operation and Development Screening Information Data Set
 World Health Organization

Revision date 06-10-2024

This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage,

transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet