



TECHNICAL INFORMATION

Watts:	100
Lumens:	14000
Input Power:	AC:176-305V, 50Hz
Long Life:	30,000 Hours
Unit Color:	Grey
Body Type:	Aluminum
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>70
Operation Temperature:	-20°C to +45°C
Dimmable:	Yes
Beam Angle:	153x70°
Color Temperature:	5700K
Dimension:	656.4x270x85mm
Output Voltage:	57-171VDC
Output Current:	700-1050mA


140 LUMENS STREETLIGHTS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 884 - 934 939

[View more details](#)



FEATURES

- Powerful LED light source with lumen efficiency of 140 LM/W
- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- Adjustable adaptor with mounting diameter of 60mm
- Designed with Inventronics driver
- Designed with Class II and Type III Lens with beam angle of 153x70°
- Suitable for industrial usage, warehouses, highways etc.

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 6.4
Unit CBM: 0.0325325
Dimension: 656.4x270x85mm

MASTER BOX PACKAGING

Box Qty: 2
Qty Per Pallet: 40
Length (Box) mm: 350
Width (Box) mm: 715
Height (Box) mm: 130

LISTING DETAILS

Commodity Code: 9405403990
Ean Code: 3800157646024