


MINIATURE ALUMINUM ELECTROLYTIC CAPACITORS

WF High ripple current, Extremely Low Impedance Series

S
Solvent Proof

- Operating temperature range of $-40 \sim +105^{\circ}\text{C}$
- Extremely low impedance at high frequency
- High reliability withstanding 10000 hours load life at 105°C
(5000 / 7000 hours for smaller case size as specified below)
- Complied to the RoHS directive


WL → WF
Long life



Item	Characteristics								
Operating temperature range	$-40 \sim +105^{\circ}\text{C}$								
Leakage current max.	$I = 0.03\text{CV}$ or $3\mu\text{A}$ whichever is greater (after 2 minutes)								
Capacitance tolerance	$\pm 20\%$ at 120Hz, 20°C								
Dissipation factor max. (at 120Hz, 20°C)	WV	6.3	10	16	25	35	50	63	100
	$\tan\delta$	0.22	0.19	0.16	0.14	0.12	0.10	0.09	0.08
Low temperature characteristics (Impedance ratio at 120Hz)	WV	6.3	10	16	25	35	50	63	100
	Z-40°C/Z+20°C	8	6	4	3				
Load life (after application of the rated voltage for 10000 hours at 105°C)	Leakage current	Less than specified value							
	Capacitance change	Within $\pm 25\%$ of initial value							
	$\tan\delta$	Less than 200% of specified value							
	$\varnothing D$	$\varnothing D = 5, 6.3$		$\varnothing D = 8, 10$		$\varnothing D \geq 12.5$			
	Life time	5000 hours		7000 hours		10000 hours			
Shelf life (at 105°C)	After 1000 hours no load test, leakage current, capacitance and $\tan\delta$ are same as load life value.								

DRAWING

Unit : mm



$\varnothing D$	5	6.3	8	10	12.5	16	18
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5
$\varnothing d$	0.5	0.5	0.6	0.6	0.6	0.8	0.8
β	1.5				2.0		

FREQUENCY COEFFICIENT OF PERMISSIBLE RIPPLE CURRENT

$\mu\text{F} \backslash \text{Frequency(Hz)}$	120	1k	10k	100k \leq
~ 33	0.40	0.65	0.82	1.00
39 ~ 270	0.50	0.70	0.84	1.00
330 ~ 680	0.55	0.75	0.86	1.00
820 ~ 1800	0.60	0.80	0.88	1.00
2200 ~ 15000	0.70	0.85	0.90	1.00

WF series

● DIMENSIONS & MAXIMUM PERMISSIBLE RIPPLE CURRENT

WV Item μF	6.3			10			16			25		
	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz
33										5 × 11	0.90	150
47							5 × 11	0.90	150	5 × 11	0.90	150
100	5 × 11	0.90	150	5 × 11	0.90	150	6.3 × 11	0.40	250	6.3 × 11	0.40	250
220	6.3 × 11	0.40	250	6.3 × 11	0.40	250	8 × 11.5	0.25	400	8 × 11.5	0.25	400
330	6.3 × 11	0.40	250	8 × 11.5	0.25	400	8 × 11.5	0.25	400	10 × 12.5	0.16	580
470	8 × 11.5	0.25	400	8 × 11.5	0.25	400	10 × 12.5	0.16	580	10 × 16	0.120	770
1000	10 × 12.5	0.16	580	10 × 16	0.120	770	10 × 20	0.078	1050	12.5 × 20	0.062	1300
2200	12.5 × 20	0.062	1300	12.5 × 20	0.062	1300	12.5 × 25	0.048	1650	16 × 25	0.034	1850
3300	12.5 × 20	0.062	1300	12.5 × 25	0.048	1650	16 × 25	0.034	1850	16 × 31.5	0.029	2000
4700	16 × 25	0.034	1850	16 × 25	0.034	1850	16 × 31.5	0.029	2000	18 × 35.5	0.025	2200
6800	16 × 25	0.034	1850	16 × 31.5	0.029	2000	18 × 35.5	0.025	2200			
10000	16 × 31.5	0.029	2000	18 × 35.5	0.025	2200						
15000	18 × 35.5	0.025	2200									

WV Item μF	35			50			63			100		
	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz	$\varnothing D \times L$ (mm)	Impedance (Ω)max. 20°C 100kHz	Ripple current (mA rms) 105°C 100kHz
0.47				5 × 11	5.5	17				5 × 11	6.0	15
1.0				5 × 11	4.0	30				5 × 11	4.5	20
2.2				5 × 11	2.5	43				5 × 11	3.0	30
3.3				5 × 11	2.2	53				5 × 11	2.7	40
4.7				5 × 11	1.9	88				5 × 11	2.5	65
10				5 × 11	1.5	100	5 × 11	2.3	87	6.3 × 11	1.2	140
22				5 × 11	0.9	150	6.3 × 11	1.30	140	8 × 11.5	0.63	160
33	5 × 11	0.90	150	6.3 × 11	0.40	250	6.3 × 11	1.20	140	10 × 12.5	0.43	230
47	6.3 × 11	0.40	250	6.3 × 11	0.40	250	8 × 11.5	0.63	210	10 × 16	0.31	290
100	8 × 11.5	0.25	400	8 × 11.5	0.25	400	10 × 12.5	0.43	300	12.5 × 20	0.16	430
220	10 × 12.5	0.16	580	10 × 16	0.12	770	10 × 25	0.210	520	16 × 25	0.073	900
330	10 × 16	0.120	770	10 × 20	0.08	1050	12.5 × 20	0.160	660	16 × 25	0.073	900
470	10 × 20	0.078	1050	12.5 × 20	0.062	1300	12.5 × 25	0.120	750			
1000	12.5 × 25	0.048	1650	16 × 25	0.034	1850	16 × 31.5	0.054	1390			
2200	16 × 31.5	0.029	2000	18 × 35.5	0.025	2200						
3300	18 × 35.5	0.025	2200									