


Features:

- High brightness LEDs
- Under voltage shutdown (<24V)
- Low power consumption (<0,2W)
- Long lifetime (>20000h)
- Fail-safe
- According DIN EN50155 class TX

Dimensions:



Lamp base in accordance to DIN EN 60061-1: BA9s

Technical Data:

Colour:		white	
Wavelength:	peak		
Wavelength:	dominant		
Colour temperature:	typical	9500	K
Chromaticity coordinate:			
Luminous intensity:	typical	1,2	lm
Viewing angle:		120	°

Voltage	nominal	72	V
Voltage	rated	82,8	V
Voltage	lowest perm.	50,4	V
Voltage	highest perm.	90	V
Voltage	non-perm.	43,2	V
Voltage	Non-perm.	100,8	V
Current	typical	2,2	mA
Power consumption	typical	<0,2	W

Durability	min	20.000	h
Storage temperature		-40 +80	°C
Ambient temperature		-40 +80	°C

Marking info label of origin ; nominal voltage ; production code

Standards achieved DIN EN 50155 compliant

Specials 4 LEDs in series are used to illuminate the lamp while 2x2 LEDs are protected. In case one LED fails the other pair of still functioning LEDs is working. The light output is half in order to indicate the malfunction and the need for replacement.

General:

Due to production tolerances of the LED, colour temperature variations may be detected within individual consignments. Illumination and electrical data are measured at DC operating and an ambient temperature of 25°C. Colour Coordinates Measurement allowance is ± 0.01. Durability estimated at nominal voltage and 25°C ambient temperature.

Product_Datasheet_18824A3W_rev_ b.doc	RAS	Revision: b	Date:18.07.2011
CML Technologies GmbH & Co. KG, 67098 Bad Dürkheim / Germany Tel.: +49 6322 9567- 0, Fax: +49 6322 9567- 88			