



SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Name of product Pluvonin Spray China

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended intended purpose(s)

waterproofing agent

1.3. Details of the supplier of the safety data sheet

Manufacturer

F.W.Klever
Hauptstraße 20, D-84168 Aham
Phone +49 (0) 8744 96 99 10, Fax + 49 (0) 8744 96 99 96
E-Mail info@ballistol.de
Internet www.ballistol.de

Advice

Qualitätssicherung
Phone +49 (0) 8744 96 99 30
E-mail (competent person):
info@ballistol.de

1.4. Emergency telephone number

Emergency advice

Dr.Zettler (Werktags von 8.00 Uhr bis 16.00 Uhr) oder
Giftnotrufzentrale 022819240
Phone +49 (0) 8744 96 99 30
This number is only available at office times.

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP/GHS]

Hazard classes and Hazard categories	Hazard Statements	Classification procedure
Aerosol 1	H222, H229	
Skin Irrit. 2	H315	
STOT SE 3	H336	
Aquatic Chronic 2	H411	

Hazard statements for physical hazards

H222 Extremely flammable aerosol.
H229 Pressurised container: May burst if heated.

Hazard statements for health hazards

H315 Causes skin irritation.
H336 May cause drowsiness or dizziness.

Hazard statements for environmental hazards

H411 Toxic to aquatic life with long lasting effects.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008 [CLP/GHS]



GHS02



GHS07



GHS09

Signal word

Danger

Hazard statements for physical hazards

H222 Extremely flammable aerosol.
H229 Pressurised container: May burst if heated.

Hazard statements for health hazards

H315 Causes skin irritation.
H336 May cause drowsiness or dizziness.

Hazard statements for environmental hazards

H411 Toxic to aquatic life with long lasting effects.

Precautionary Statements

General

P102 Keep out of reach of children.

Prevention

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.
No smoking.
P211 Do not spray on an open flame or other ignition source
P251 Do not pierce or burn, even after use.
P261 Avoid breathing dust/fume/gas/mist/vapours/spray.
P271 Use only outdoors or in a well-ventilated area.
P273 Avoid release to the environment.

Response

P301 + P310 IF SWALLOWED: Immediately call a POISON CENTER/doctor/...
P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P312 Call a POISON CENTER/doctor/.../if you feel unwell.
P331 Do NOT induce vomiting.

Storage

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.
P405 Store locked up.
P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

Disposal

P501 Dispose of contents/container to ...
P501 Dispose of contents/container to recycling

Additional information

Remark

Pluvonin ist ozonneutral

2.3. Other hazards

No information available.



SECTION 3: Composition/ information on ingredients

3.1. Substances

not applicable

3.2. Mixtures

Description

Name: silicone (unspecified) in solvent (hydrocarbon C9-C12, CAS 1174921-79-9) Conc: 5-10%

Hazardous ingredients

CAS No	EC No	Name	[% weight]	Classification according to Regulation (EC) No 1272/2008 [CLP/ GHS]
74-98-6	200-827-9	propane	ca. 10	Flam. Gas 1, H220 / Press. Gas
106-97-8	203-448-7	butane	ca. 20	Flam. Gas 1, H220 / Press. Gas
107-83-5	203-523-4	hexane (containing < 5 % n-hexane (203-777-6))	ca. 60	Flam. Liq. 2, H225 / Asp. Tox. 1, H304 / Skin Irrit. 2, H315 / STOT SE 3, H336 / Aquatic Chronic 2, H411

SECTION 4: First aid measures

4.1. Description of first aid measures

In case of inhalation

Ensure of fresh air.

In the event of symptoms refer for medical treatment.

In case of skin contact

In case of contact with skin wash off with soap and water.

In case of eye contact

In case of contact with eyes rinse with plenty of water carefully. In the event of persistent symptoms seek medical treatment.

In case of ingestion

Do not induce vomiting.

Give plenty of water to drink in small sips.

4.2. Most important symptoms and effects, both acute and delayed

No information available.

4.3. Indication of any immediate medical attention and special treatment needed

Treatment (Advice to doctor)

Treat symptoms.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Foam

ABC powder

Carbon dioxide

Water spray jet

Unsuitable extinguishing media

Strong water jet

5.2. Special hazards arising from the substance or mixture

In the event of fire the following can be released:

Nitrogen oxides (NO_x)

Carbon dioxide (CO₂)

5.3. Advice for firefighters

Special protective equipment for fire-fighters

Use breathing apparatus with independent air supply (isolated).

Additional information

Cool endangered containers with water spray jet.

Heating causes rise in pressure with risk of bursting

Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Keep away sources of ignition.

Use breathing apparatus if exposed to vapours/dust/aerosol.

6.2. Environmental precautions

Do not discharge into the drains/surface waters/groundwater.

6.3. Methods and material for containment and cleaning up

Suck off by room ventilation.

Clean contaminated objects and floor thoroughly under consideration of environment regulations.

6.4. Reference to other sections

No information available.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

Care for thoroughly room ventilation, if necessary use in well ventilated area with local exhaust ventilation at workplace.

Do not spray into flames or ignition sources

Hygiene measures

Remove soiled or soaked clothing immediately.

Wash hands before breaks and after work.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking

Protect aerosols from temperatures exceeding 50°C

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep only in original container.

Further information on storage conditions

Recommended storage temperature: room temperature.



Information on storage stability

At appropriate storage unlimited stability.

Storage group 2B

7.3. Specific end use(s)

No information available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.2. Exposure controls

Respiratory protection

Respiratory protection must be worn whenever the WEL levels have been exceeded

The following applies to propane in general: If the concentration is exceeded, closed-circuit breathing apparatuses must be used

Use filter apparatus type AX, identification colour brown according to EN 371

Hand protection

Ballistol is dermatologically tested and rated "very good", so that the hand guard or the skin is not necessary.

Eye protection

With demand: protective glasses

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

aerosol

Colour

light yellow

Odour

characteristic

Odour threshold

not determined

Important health, safety and environmental information

	Value	Temperature	at	Method	Remark
pH value	not determined				
boiling point	-48 °C				(Propan)
Melting point / Freezing point	not determined				
Flash point	ca. -104 °C				(Propan)
Vapourisation rate	not determined				
Flammable (solid)	not determined				
Flammability (gas)	not determined				
Ignition temperature	not determined				



	Value	Temperature	at	Method	Remark
Self ignition temperature	not determined				
Lower explosion limit	ca. 1,5 Vol-%				(Propan)
Upper explosion limit	10,9 Vol-%				(Propan)
Vapour pressure	not determined				
Relative density	ca. 0,69 g/ml	20 °C		1013 hPa	information concerns to liquid phase
Vapour density	not determined				
Solubility in water		20 °C		1013 hPa	more or less insoluble
Solubility/other	not determined				
Partition coefficient n-octanol/water (log P O/W)	not determined				
Decomposition temperature	not determined				
Viscosity	not determined				
Oxidising properties No information available.					
Explosive properties No information available.					
9.2. Other information No information available.					

SECTION 10: Stability and reactivity

10.1. Reactivity

No information available.

10.2. Chemical stability

No information available.

10.3. Possibility of hazardous reactions

No information available.

10.4. Conditions to avoid

Container under pressure. Protect from direct exposure to sunlight and temperatures exceeding 50°C.

10.5. Incompatible materials

Substances to avoid

Reactions with strong oxidising agents.

10.6. Hazardous decomposition products

Carbon monoxide and carbon dioxide.

Additional information

Product is stable under normal storage conditions

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity/Irritation/Sensitization

	Value/Validation	Species	Method	Remark
LD50 acute oral	> 5000 mg/kg	rat		Information concerns to main component.
LD50 acute dermal	> 2000 mg/kg	rabbit		Data refer to the main component
LC50 acute inhalation	> 20 mg/l (4 h)	rat	OECD 403	Details refer to the main component
Skin irritation	low irritant effect			
Eye irritation	non-irritant			
Skin sensitization	non-sensitizing			

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicological effects

	Value	Species	Method	Validation
Fish	LC50 > 1 mg/l (48 h)	Oryzias Latipes		Information are based on results of similar products
Daphnia	EC50 2,1 Mikro-g/l (48 h)	Daphnia magna		Based on actual testing result data or a comparable product
Algae	NOEC 30 mg/l (72 h)	Pseudokirchneriella subcapitata (Grünalge)		Based on actual testing result data or a comparable product

12.2. Persistence and degradability

	Elimination rate	Method of analysis	Method	Validation
Biological degradability	vrednotijo			Biodegradable

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil



No information available.

12.5. Results of PBT and vPvB assessment

No information available.

12.6. Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Recommendations for packaging

Contaminated packaging should be emptied as far as possible and after appropriate cleansing may be taken for reuse.

Barrel: return by DSD (Dualistic System Germany)

! SECTION 14: Transport information

	ADR/RID	IMDG	IATA-DGR
14.1. UN number	-	1950	1950
14.2. UN proper shipping name	-	Aerosol (Propano)	Aerosols flammable (Propano)
14.3. Transport hazard class(es)	-	2	2.1
14.4. Packing group	-	-	-
14.5. Environmental hazards	-	No	No

14.6. Special precautions for user

No information available.

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

No information available.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

Water hazard class 2 self-classification

15.2. Chemical Safety Assessment

For this substance a chemical safety assessment is not required.

SECTION 16: Other information

Recommended uses and restrictions

National and local regulations concerning chemicals shall be observed.

Further information

The information contained herein is based on the state of our knowledge. It characterizes the product with regard to the appropriate safety precautions. It does not represent a guarantee of the properties of the product.

Indication of changes: "!" = Data changed compared with the previous version. Previous version: 4.9

H220	Extremely flammable gas.
H225	Highly flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.