

# Datasheet

Steckernetzgerät für Terminals

Artikelnummer: 12002

# EDACPOWER ELECTRONICS CO., LTD. EA1018B-2E(07)/ HISTORY

Item	Revision	Description	Date	Remark
1	0	Original	2011-05-30	
2	1	Remove TUV/GS safety logo and add customer address on label.	2014-09-04	

# Index

- 1. General Description
- 2. Input Electrical Specification
- 3. Output Electrical Specification
- 4. Reliability Specification
- 5. Environmental Specification
- 6. Safety Specification
- 7. Mechanical Specification

#### 1. General Description

The purpose of this document is to specify a single phase AC input switching power supply with full range AC . The product is AC to DC switch mode power supply that provide single output EA1018B-2E -12V @1.5A max with 18W max DC output with constant voltage source. This Specification defines the input, output, performance characteristics, environment , noise and safety requirement.

#### 2. Input Electrical Specification

#### 2-1. AC Input Voltage

Maximum Voltage: 264Vrms

Normal Voltage: 100~240Vrms

Minimum Voltage: 90Vrms

#### 2-2. AC Input Frequency

Maximum Frequency: 63Hz
Normal Frequency: 50~60Hz
Minimum Frequency: 47Hz

# 2-3. Input Current

a.1.0 A (Max.) @ AC 100Vrms input with full load. b.0.75A (Max.) @ AC 240Vrms input with full load.

#### 2-4. Efficiency

Meet CEC level V

Nameplate Output Power	<b>Energy Star Spec</b>
0 to 1 Watt	0.48xPno+0.14
> 1 50 Watts	0.0626xLn(Pno)+0.622
> 50 to 250 Watts	0.87

80.29% minimum at normal line input and average of 25%, 50%, 75%, 100% of max load.

#### 2-5. Configuration

2-wire AC input (Line Neutral)

#### 2-6. Input Fuse

The Line of the AC input shall have a fuse, rated is T2A/250V

#### 2-7. Inrush Current

30A at 110 Vac

60A at 240 Vac At cold start, nominal load.

#### 2-8. No load Power Consumption:

**Less then 0.3 Watts.** at normal line.

# 2-9. Hold Up Time

10 mSec., @ Normal line, with full load.

#### 2-10. Rise Time

20 mSec. @ min Input voltage, with full load.

From 10% to 90% of output voltage.

#### 2-11. Turn-ON Time

The output voltage should rise to 90% of rated output voltage in less than 3 seconds from AC apply to low line voltage start up.

#### 3. Output Electrical Specification

#### 3-1. Output Voltage and Current

Output Voltage	Min Current(A)	Max Current(A)
<u>+12V</u>	0A	<u>1.5A</u>

#### 3-2. Line / Load Regulation

	Output Voltage (V)	Tolerance (%)	Regulation(V)
Vo	+12V	+5% ~ -5%	11.4 ~ 12.6V

#### 3-3. Dynamic Load Regulation

<u>±5%</u> excursion from 50% to 100% load and back to 50% load change of DC output at any frequency up to 1KHz(duty 50%)

#### 3-4. Ripple & Noise

The power supply shall not exceed the following limits on the indicated voltage for 60Hz or 50Hz ripple, Switching frequency ripple & noise and measured with a 20MHz bandwidth and output parallel with a 0.1uF ceramic capacitor and a 47uF electrolytic capacitor to ground. Temperature at 25°C and nominal AC input voltage

Output	Ripple/Noise
12V	240mV max

Ripple / Noise: 60Hz ripple + switching ripple and noise

#### **3-5.** Short circuit protection:

The output should shut-down when subjected to a short circuit(R<0.3R). After shut-down the power supply shall return to normal operating conditions after removing the short situation .

#### **3-7. Over Power Protection**:

180% of max current

When Over-Power occurred the output should be shut down and the over –current Situation is removed the output shall be auto-recover without any harm .

# 3-8. Stability

2% Max. at constant load with constant input (after 30 minutes of operation).

#### 3-9. Temperature Rise

Less than 45°C on top/bottom case at normal AC input & 80% load of DC output at environment temperature 25 °C.

#### **3-10. Drop-out (Power Line Disturbance)**

Output voltage shall remain within the specified regulation range, through the absence of a line input during 1/2 cycle, at full load and normal AC line input

#### 4. Reliability Specification

#### 4-1. MTBF (MIL-STD-781C)

The power supply shall be designed and produced to have a mean time between failures (MTBF) of 30000 operating hours minimum conditions: 80% maximum load at 25 °C, nominal input voltage.

#### **5. Environment Specification**

#### **5-1 Temperature**

a. Operating: 0 to 40°Cb. Storage: -20 to 85°C

#### 5-2 Humidity

a. Operating: 10 to 90 %b. Storage: 5 to 95 %

#### 5-3 Altitude

From sea level to 2,000 Meter (operation) and 5,000 Meter (non operation)

# 6-0. Safety Specification

#### 6-1. Hi-Pot Test

3000VAC 10mA 3 Sec or 4242VDC 5mA 3 Sec. between primary and secondary circuit

#### **6-2. Insulation Test**

500 Vdc, 3 Sec. between primary and secondary circuit IR should 100 M.

# 6-3. Leakage Current

**250 uA** @ 240VAC 50Hz

# 6-4. Safety

CE

#### 6-5. EMI

Comply with Standards

CISPR 22, EN 55022 Class B

FCC PART 15 Class B


# 7. Mechanical Specification


**7-1. Physical Size:** 72 L x 34W x 51 H (mm)


**7-2. Enclosure material:** 94V-0 minimum


7-3. Output Cable (Reference) : <u>UL2725 #28</u>+#24

7-4. Net Weight (Reference): 152 gm









EDAC POWER ELEC.				APPROVED
MODEL	EA1018B-2E(07)	UNIT	mm	DESIGNED
color	BLACK	SCALE		CHECK
cus.		DATE	2011-05-30	drawing L.J.YU