

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 1 of 11

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Kisling - 5011

UFI:

Q7C0-N03G-Y00S-Q0J3

1.2. Relevant identified uses of the substance or mixture and uses advised against**Use of the substance/mixture**

Adhesives and sealants

Uses advised against

No information available.

1.3. Details of the supplier of the safety data sheet**Manufacturer**

Company name: Kisling AG
Street: Motorenstrasse 102
Place: CH-8620 Wetzikon
Telephone: +41 58 272 0 272
E-mail: customerservice@kisling.com
Internet: www.kisling.com

Supplier

Company name: Kisling (Deutschland) GmbH
Street: Salzstraße 15
Place: D-74676 Niedernhall
Telephone: +49 7940 50961 61
E-mail: customerservice@kisling.com
Contact person: Dr. Hans Götz Telephone: +49 7940 5096 143
E-mail: compliance@kisling.com
Internet: www.kisling.com

1.4. Emergency telephone number:

24 hr. emergency phone number +1 872 5888271 (KAR)
Medicines & Poisons Info Office +356 2545 6508

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Regulation (EC) No 1272/2008**

Skin Irrit. 2; H315
Eye Irrit. 2; H319
STOT SE 3; H335

Full text of hazard statements: see SECTION 16.

2.2. Label elements**Regulation (EC) No 1272/2008****Hazard components for labelling**

ethyl 2-cyanoacrylate

Signal word: Warning**Pictograms:**

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 2 of 11

Hazard statements

- H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

Precautionary statements

- P101 If medical advice is needed, have product container or label at hand.
P271 Use only outdoors or in a well-ventilated area.
P280 Wear protective gloves and eye/face protection.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P405 Store locked up.

Special labelling of certain mixtures

- EUH202 Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Labelling of packages where the contents do not exceed 125 ml

Signal word: Warning

Pictograms:



Hazard statements

H335

Precautionary statements

P101-P271-P405

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Chemical characterization

Mixture of substances listed below with nonhazardous components.

Hazardous components

CAS No	Chemical name			Quantity
	EC No	Index No	REACH No	
	Classification (Regulation (EC) No 1272/2008)			
7085-85-0	ethyl 2-cyanoacrylate			50 - < 100 %
	230-391-5	607-236-00-9		
	Skin Irrit. 2, Eye Irrit. 2, STOT SE 3; H315 H319 H335			

Full text of H and EUH statements: see section 16.

Specific Conc. Limits, M-factors and ATE

CAS No	EC No	Chemical name	Quantity
	Specific Conc. Limits, M-factors and ATE		
7085-85-0	230-391-5	ethyl 2-cyanoacrylate	50 - < 100 %
	dermal: LD50 = > 2000 mg/kg; oral: LD50 = > 5000 mg/kg STOT SE 3; H335: >= 10 - 100		

SECTION 4: First aid measures

4.1. Description of first aid measures

General information

Take off immediately all contaminated clothing.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 3 of 11

After inhalation

Provide fresh air. If breathing is irregular or stopped, administer artificial respiration. Medical treatment necessary. When in doubt or if symptoms are observed, get medical advice.

After contact with skin

After contact with skin, wash immediately with plenty of water and soap. Take off immediately all contaminated clothing and wash it before reuse. Medical treatment necessary. After contact with skin, wash immediately with plenty of water and soap. In case of skin irritation, consult a physician.

After contact with eyes

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Remove contact lenses, if present and easy to do. Continue rinsing.

After ingestion

Observe risk of aspiration if vomiting occurs. Rinse mouth immediately and drink 1 glass of water. Do NOT induce vomiting. Get immediate medical advice/attention.

4.2. Most important symptoms and effects, both acute and delayed

No further relevant information available.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically. No further relevant information available.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media

Co-ordinate fire-fighting measures to the fire surroundings. Co-ordinate fire-fighting measures to the fire surroundings.

Unsuitable extinguishing media

No information available.

5.2. Special hazards arising from the substance or mixture

In case of fire and/or explosion do not breathe fumes.

5.3. Advice for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing. Full protection suit.

Additional information

Use water spray jet to protect personnel and to cool endangered containers. Suppress gases/vapours/mists with water spray jet. Collect contaminated fire extinguishing water separately. Do not allow entering drains or surface water.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General advice

Provide adequate ventilation. Do not breathe gas/fumes/vapour/spray. Avoid contact with skin, eyes and clothes. Use personal protection equipment. Provide adequate ventilation. Wear breathing apparatus if exposed to vapours/dusts/aerosols.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. In case of gas escape or of entry into waterways, soil or drains, inform the responsible authorities.

6.3. Methods and material for containment and cleaning up

For cleaning up

Absorb with liquid-binding material (sand, diatomaceous earth, acid- or universal binding agents). Treat the recovered material as prescribed in the section on waste disposal.

6.4. Reference to other sections

Safe handling: see section 7

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 4 of 11

Personal protection equipment: see section 8

Disposal: see section 13

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Advice on safe handling

No special handling advices are necessary.

Advice on protection against fire and explosion

No special fire protection measures are necessary.

Advice on general occupational hygiene

Remove contaminated, saturated clothing immediately. Draw up and observe skin protection programme.

Wash hands and face before breaks and after work and take a shower if necessary. When using do not eat, drink, smoke, sniff.

Further information on handling

Keep only in the original container in a cool, well-ventilated place.

7.2. Conditions for safe storage, including any incompatibilities

Requirements for storage rooms and vessels

Keep container tightly closed. Keep locked up. Store in a place accessible by authorized persons only. Provide adequate ventilation as well as local exhaust at critical locations.

Hints on joint storage

none

Further information on storage conditions

Store in a cool dry place. Protect from direct sunlight.

7.3. Specific end use(s)

No further relevant information available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

DNEL/DMEL values

CAS No	Name of agent			
DNEL type		Exposure route	Effect	Value
7085-85-0	ethyl 2-cyanoacrylate			
Worker DNEL, long-term		inhalation	systemic	9,25 mg/m³
Worker DNEL, acute		inhalation	systemic	9,25 mg/m³
Worker DNEL, long-term		inhalation	local	9,25 mg/m³
Worker DNEL, acute		inhalation	local	9,25 mg/m³
Consumer DNEL, long-term		inhalation	systemic	9,25 mg/m³
Consumer DNEL, acute		inhalation	systemic	9,25 mg/m³
Consumer DNEL, long-term		inhalation	local	9,25 mg/m³
Consumer DNEL, acute		inhalation	local	9,25 mg/m³

8.2. Exposure controls



Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 5 of 11

Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Individual protection measures, such as personal protective equipment

Eye/face protection

Suitable eye protection: goggles.

Hand protection

Hand protection EN ISO 374

When handling with chemical substances, protective gloves must be worn with the CE-label including the four control digits. The quality of the protective gloves resistant to chemicals must be chosen as a function of the specific working place concentration and quantity of hazardous substances. For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. Tested protective gloves must be worn.

For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves.

Skin protection

Wear suitable protective clothing. The type of personal protection equipment has to be chosen based on the concentration and amount of the dangerous substance at the workplace.

Respiratory protection

In case of inadequate ventilation wear respiratory protection. If technical exhaust or ventilation measures are not possible or insufficient, respiratory protection must be worn.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	transparent
Odour:	characteristic
Odour threshold:	not determined
Melting point/freezing point:	-22 °C
Boiling point or initial boiling point and boiling range:	> 200 °C
Flammability:	not applicable
Lower explosion limits:	not determined
Upper explosion limits:	not determined
Flash point:	80 - 93 °C
Auto-ignition temperature:	485 °C
Decomposition temperature:	not determined
pH-Value:	not determined
Viscosity / kinematic:	not determined
Water solubility:	not determined
Solubility in other solvents	not determined
Partition coefficient n-octanol/water:	not determined
Vapour pressure:	not determined
Density (at 25 °C):	1,10 g/cm³
Relative density:	not determined
Relative vapour density:	not determined

9.2. Other information

Information with regard to physical hazard classes

Explosive properties

The product is not: Explosive.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 6 of 11

Oxidizing properties
not determined

Other safety characteristics

Evaporation rate: not determined
Solid content: not determined
Viscosity / dynamic:
(at 25 °C) 10-30 mPa·s

SECTION 10: Stability and reactivity

10.1. Reactivity

No further relevant information available.

10.2. Chemical stability

The product is stable under storage at normal ambient temperatures.

10.3. Possibility of hazardous reactions

No known hazardous reactions.

10.4. Conditions to avoid

The product is chemically stable under recommended conditions of storage, use and temperature.

10.5. Incompatible materials

No further relevant information available.

10.6. Hazardous decomposition products

No further relevant information available.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Toxicokinetics, metabolism and distribution

No data available

Acute toxicity

Based on available data, the classification criteria are not met.

ATEmix calculated

ATE (oral) > 2000 mg/kg; ATE (dermal) > 2000 mg/kg; ATE (inhalation vapour) > 20 mg/l; ATE (inhalation dust/mist) > 5 mg/l

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
7085-85-0	ethyl 2-cyanoacrylate				
	oral	LD50 > 5000 mg/kg	Rat	Study report (1973)	OECD Guideline 423
	dermal	LD50 > 2000 mg/kg	Rabbit	Study report (1973)	OECD Guideline 402

Irritation and corrosivity

Causes skin irritation.
Causes serious eye irritation.

Sensitising effects

Based on available data, the classification criteria are not met.

Carcinogenic/mutagenic/toxic effects for reproduction

Based on available data, the classification criteria are not met.

STOT-single exposure

May cause respiratory irritation. (ethyl 2-cyanoacrylate)

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 7 of 11

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

Specific effects in experiment on an animal

No data available

Additional information on tests

No data available

Practical experience

May be harmful if swallowed, in contact with skin or if inhaled.

11.2. Information on other hazards

Further information

The mixture is classified as hazardous according to regulation (EC) No 1272/2008 [CLP].

SECTION 12: Ecological information

12.1. Toxicity

Based on available data, the classification criteria are not met.

12.2. Persistence and degradability

No data available

CAS No	Chemical name			
	Method	Value	d	Source
	Evaluation			
7085-85-0	ethyl 2-cyanoacrylate			
	OECD 301D	57%		

12.3. Bioaccumulative potential

No data available

Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
7085-85-0	ethyl 2-cyanoacrylate	0,776

12.4. Mobility in soil

No further relevant information available.

12.5. Results of PBT and vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6. Endocrine disrupting properties

This product does not contain a substance that has endocrine disrupting properties with respect to non-target organisms as no components meets the criteria.

12.7. Other adverse effects

No data available

Further information

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Disposal recommendations

Do not allow to enter into surface water or drains. Do not allow to enter into soil/subsoil. Dispose of waste according to applicable legislation.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 8 of 11

List of Wastes Code - residues/unused products

080410 WASTES FROM THE MANUFACTURE, FORMULATION, SUPPLY AND USE (MFSU) OF COATINGS (PAINTS, VARNISHES AND VITREOUS ENAMELS), ADHESIVES, SEALANTS AND PRINTING INKS; wastes from MFSU of adhesives and sealants (including waterproofing products); waste adhesives and sealants other than those mentioned in 08 04 09

List of Wastes Code - used product

080410 WASTES FROM THE MANUFACTURE, FORMULATION, SUPPLY AND USE (MFSU) OF COATINGS (PAINTS, VARNISHES AND VITREOUS ENAMELS), ADHESIVES, SEALANTS AND PRINTING INKS; wastes from MFSU of adhesives and sealants (including waterproofing products); waste adhesives and sealants other than those mentioned in 08 04 09

List of Wastes Code - contaminated packaging

080410 WASTES FROM THE MANUFACTURE, FORMULATION, SUPPLY AND USE (MFSU) OF COATINGS (PAINTS, VARNISHES AND VITREOUS ENAMELS), ADHESIVES, SEALANTS AND PRINTING INKS; wastes from MFSU of adhesives and sealants (including waterproofing products); waste adhesives and sealants other than those mentioned in 08 04 09

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information

Land transport (ADR/RID)

- 14.1. UN number or ID number:**
14.2. UN proper shipping name:
14.3. Transport hazard class(es):
14.4. Packing group:

No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.

Inland waterways transport (ADN)

- 14.1. UN number or ID number:**
14.2. UN proper shipping name:
14.3. Transport hazard class(es):
14.4. Packing group:

No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.

Marine transport (IMDG)

- 14.1. UN number or ID number:**
14.2. UN proper shipping name:
14.3. Transport hazard class(es):
14.4. Packing group:

No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.
 No dangerous good in sense of this transport regulation.

Air transport (ICAO-TI/IATA-DGR)

- 14.1. UN number or ID number:**
14.2. UN proper shipping name:
14.3. Transport hazard class(es):
14.4. Packing group:

UN 3334
 AVIATION REGULATED LIQUID, N.O.S.
 9
 III
 9

Hazard label:



Special Provisions:

Limited quantity Passenger:

Passenger LQ:

Excepted quantity:

IATA-packing instructions - Passenger:

IATA-max. quantity - Passenger:

IATA-packing instructions - Cargo:

A27
 30 kg G
 Y964
 E1
 964
 450 L
 964

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 9 of 11

IATA-max. quantity - Cargo:

450 L

14.5. Environmental hazards

ENVIRONMENTALLY HAZARDOUS: No

14.6. Special precautions for user

No information available.

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 3

2010/75/EU (VOC): < 2 %

National regulatory information

Employment restrictions: Observe restrictions to employment for juveniles according to the 'juvenile work protection guideline' (94/33/EC).

Water hazard class (D): 1 - slightly hazardous to water

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

SECTION 16: Other information

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 10 of 11

Abbreviations and acronyms

CLP: Classification, labelling and Packaging
 REACH: Registration, Evaluation and Authorization of Chemicals
 GHS: Globally Harmonised System of Classification, Labelling and Packaging of Chemicals
 UN: United Nations
 CAS: Chemical Abstracts Service
 DNEL: Derived No Effect Level
 DMEL: Derived Minimal Effect Level
 PNEC: Predicted No Effect Concentration
 ATE: Acute toxicity estimate
 LC50: Lethal concentration, 50%
 LD50: Lethal dose, 50%
 LL50: Lethal loading, 50%
 EL50: Effect loading, 50%
 EC50: Effective Concentration 50%
 ErC50: Effective Concentration 50%, growth rate
 NOEC: No Observed Effect Concentration
 BCF: Bio-concentration factor
 PBT: persistent, bioaccumulative, toxic
 vPvB: very persistent, very bioaccumulative
 ADR: Accord européen sur le transport des marchandises dangereuses par Route
 (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 RID: Regulations concerning the international carriage of dangerous goods by rail
 ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
 (Accord européen relatif au transport international des marchandises dangereuses par voies de navigation intérieures)
 IMDG: International Maritime Code for Dangerous Goods
 EmS: Emergency Schedules
 MFAG: Medical First Aid Guide
 IATA: International Air Transport Association
 ICAO: International Civil Aviation Organization
 MARPOL: International Convention for the Prevention of Marine Pollution from Ships
 IBC: Intermediate Bulk Container
 VOC: Volatile Organic Compounds
 SVHC: Substance of Very High Concern
 For abbreviations and acronyms, see: ECHA Guidance on information requirements and chemical safety assessment, chapter R.20 (Table of terms and abbreviations).
 Skin Irrit: Skin irritation
 Eye Irrit: Eye irritation
 STOT SE: Specific target organ toxicity - single exposure

Classification for mixtures and used evaluation method according to Regulation (EC) No 1272/2008 [CLP]

Classification	Classification procedure
Skin Irrit. 2; H315	Calculation method
Eye Irrit. 2; H319	Calculation method
STOT SE 3; H335	Calculation method

Relevant H and EUH statements (number and full text)

H315 Causes skin irritation.
 H319 Causes serious eye irritation.
 H335 May cause respiratory irritation.
 EUH202 Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Further Information

The information is based on the present level of our knowledge. It does not, however, give assurance of

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Kisling - 5011

Revision date: 18.08.2023

Product code: 5011

Page 11 of 11

product properties and establishes no contract legal rights. The receiver of our product is singularly responsible for adhering to existing laws and regulations. The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

Identified uses

No	Short title	LCS	SU	PC	PROC	ERC	AC	TF	Specification
1	Adhesives and sealants	PW, C	6a, 6b, 12, 18, 19	1	11, 19	4, 8a, 8c, 8d	4e, 4g, 5c, 6g, 7c, 7g, 8, 10, 11, 13	110	K+D

LCS: Life cycle stages
PC: Product categories
ERC: Environmental release categories
TF: Technical functions

SU: Sectors of use
PROC: Process categories
AC: Article categories

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)