

Top-up Oil 5W-40

Description

The right oil is always on board when you're on the road.

High-tech low-friction motor oil based on synthetic technology. With an improved wear protection formula. Reduces oil thickening caused by drag-in of soot. The maximum engine performance and high power reserve get you to the finish line faster and more safely. Exceeds the highest test requirements of well-known vehicle manufacturers. Assures reliable operation and maximizes the operating life of the diesel particulate filter (DPF).

Properties

- outstanding engine cleanliness
- tested for turbochargers and catalytic converters
- smooth engine running
- miscible with all commercially available motor oils
- optimum stability to aging
- high shear stability
- instant lubrication after cold start
- high lubrication reliability
- saves fuel and reduces pollutant emissions
- suitable for all common types of vehicle
- excellent low temperature behavior
- high wear resistance

Specifications / Approvals

ACEA C3 • API SN • API CF • MB-Approval 229.31 • MB-Approval 229.51 • Porsche A40 • VW 505 00 • VW 505 01

LIQUI MOLY recommends this product for vehicles or assemblies for which the following specifications or original spare part numbers are required:

BMW Longlife-04 (up to 2018) • Fiat 9.55535-H2 • Fiat 9.55535-M2 • Fiat 9.55535-S2 • Ford WSS-M2C 917-A • GM dexos2 • Renault RN 0700 • Renault RN 0710

Technical data

SAE class (engine oils)	5W-40 SAE J300
Density at 15 °C	0,855 g/cm ³ DIN 51757
Viscosity at 40 °C	88 mm ² /s ASTM D 7042-04
Viscosity at 100 °C	14,3 mm ² /s ASTM D 7042-04
Viscosity at -35 °C (MRV)	< 60000 mPas ASTM D4684
Viscosity at -30 °C (CCS)	≤ 6600 mPas ASTM D5293



Technical data

Viscosity index	169 DIN ISO 2909
HTHS at 150°C	≥ 3,5 mPas ASTM D5481
Pour point	-42 °C DIN ISO 3016
Evaporation loss (Noack)	9,5 % CEC-L-40-A-93
Flash point	232 °C DIN ISO 2592
Total base number	7,5 mg KOH/g DIN ISO 3771
Sulfate ash	≤ 0,8 g/100g DIN 51575
Color number (ASTM)	L 2,5 DIN ISO 2049

Areas of application

For all common types of vehicles with gasoline and diesel engines. Can be mixed with all commercially available motor oils.

Application

Note the operating instructions of the vehicle and engine manufacturers.

Available pack sizes

1 l Canister plastic	1305 DE
----------------------	------------

Our information is based on thorough research and may be considered reliable, although not legally binding.