

Page 1 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II (last amended by Regulation (EU) 2020/878)
Revision date / version: 27.03.2026 / 0020
Replacing version dated / version: 15.03.2024 / 0019
Valid from: 27.03.2026
PDF print date: 27.03.2026
Marine Grease

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II (last amended by Regulation (EU) 2020/878)

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Marine Grease

1.2 Relevant identified uses of the substance or mixture and uses advised against Relevant identified uses of the substance or mixture:

Lubricating grease

Uses advised against:

No information available at present.

1.3 Details of the supplier of the safety data sheet

GB

LIQUI MOLY GmbH
Jerg-Wieland-Str. 4
89081 Ulm-Lehr
Tel.: (+49) 0731-1420-0
Fax: (+49) 0731-1420-88

LIQUI MOLY UK
1310 Solihull Parkway
Birmingham Business Park
B37 7YB Solihull
Tel: +44 121 796 5365

Qualified person's e-mail address: info@chemical-check.de, k.schnurbusch@chemical-check.de Please DO NOT use for requesting Safety Data Sheets.

1.4 Emergency telephone number

Emergency information services / official advisory body:

GB

Landspítali- The National University Hospital of Iceland, tel. +354 543 2222 or 112 (valid only for Iceland)

Telephone number of the company in case of emergencies:

+49 (0) 700 / 24 112 112 (LMR)
+1 872 5888271 (LMR)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to Regulation (EC) 1272/2008 (CLP)

The mixture is not classified as dangerous in the terms of the Regulation (EC) 1272/2008 (CLP).

2.2 Label elements

Labeling according to Regulation (EC) 1272/2008 (CLP)

Not applicable

2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

The mixture does not contain any substance with endocrine disrupting properties (< 0,1 %).

SECTION 3: Composition/information on ingredients

3.1 Substances

n.a.

3.2 Mixtures

---	---
Registration number (REACH)	---
Index	---
EINECS, ELINCS, NLP, REACH-IT List-No.	---
CAS	---
content %	---
Classification according to Regulation (EC) 1272/2008 (CLP), M-factors	---

SECTION 4: First aid measures

4.1 Description of first aid measures

First-aiders should ensure they are protected!

Never pour anything into the mouth of an unconscious person!

Inhalation

Supply person with fresh air and consult doctor according to symptoms.

Skin contact

Remove polluted, soaked clothing immediately, wash thoroughly with plenty of water and soap, in case of irritation of the skin (flare), consult a doctor.

Eye contact

Remove contact lenses.

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

Ingestion

Do not induce vomiting. Consult doctor immediately.

4.2 Most important symptoms and effects, both acute and delayed

If applicable delayed symptoms and effects can be found in section 11 and the absorption route in section 4.1.

In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

4.3 Indication of any immediate medical attention and special treatment needed

Symptomatic treatment.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media

CO2

Foam

Dry extinguisher

Unsuitable extinguishing media

High volume water jet

5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Toxic gases

Oxides of carbon

Fume

5.3 Advice for firefighters

For personal protective equipment see Section 8.

In case of fire and/or explosion do not breathe fumes.

Protective respirator with independent air supply.

According to size of fire

Full protection, if necessary.

Dispose of contaminated extinction water according to official regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

6.1.1 For non-emergency personnel

In case of spillage or accidental release, wear personal protective equipment as specified in section 8 to prevent contamination.

Ensure sufficient ventilation, remove sources of ignition.

Avoid dust formation with solid or powder products.

Leave the danger zone if possible, use existing emergency plans if necessary.

Avoid contact with eyes or skin.

If applicable, caution - risk of slipping.

6.1.2 For emergency responders

See section 8 for suitable protective equipment and material specifications.

6.2 Environmental precautions

If leakage occurs, dam up.

Resolve leaks if this possible without risk.

Prevent from entering drainage system.

If accidental entry into drainage system occurs, inform responsible authorities.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent material (e.g. universal binding agent) and dispose of according to Section 13.

Or:

Pick up mechanically and dispose of according to Section 13.

6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

SECTION 7: Handling and storage

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

7.1 Precautions for safe handling

7.1.1 General recommendations

Ensure good ventilation.

Keep away from sources of ignition - Do not smoke.

Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.

Observe directions on label and instructions for use.

Do not heat to temperatures close to flash point.

7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

7.2 Conditions for safe storage, including any incompatibilities

Not to be stored in gangways or stair wells.

Store product closed and only in original packing.

7.3 Specific end use(s)

No information available at present.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II (last amended by Regulation (EU) 2020/878)

Revision date / version: 27.03.2026 / 0020

Replacing version dated / version: 15.03.2024 / 0019

Valid from: 27.03.2026

PDF print date: 27.03.2026

Marine Grease

8.2 Exposure controls

8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.

If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn.

Applies only if maximum permissible exposure values are listed here.

8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:

Tight fitting protective goggles with side protection (EN ISO 16321-1).

Skin protection - Hand protection:

Protective nitrile gloves (EN ISO 374).

Minimum layer thickness in mm:

$\geq 0,38$

Permeation time (penetration time) in minutes:

≥ 480

Protective hand cream recommended.

The breakthrough times determined in accordance with EN 16523-1 were not obtained under practical conditions.

The recommended maximum wearing time is 50% of breakthrough time.

Skin protection - Other:

Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments).

Respiratory protection:

Normally not necessary.

Thermal hazards:

Not applicable

Additional information on hand protection - No tests have been performed.

In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents.

Selection of materials derived from glove manufacturer's indications.

Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account.

Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.

In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.

The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

8.2.3 Environmental exposure controls

No information available at present.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Physical state:

Paste, solid.

Colour:

White, Light yellow

Odour:

Characteristic

Melting point/freezing point:

There is no information available on this parameter.

Boiling point or initial boiling point and boiling range:

There is no information available on this parameter.

Flammability:

There is no information available on this parameter.

Lower explosion limit:

Does not apply to solids.

Upper explosion limit:

Does not apply to solids.

Flash point:

$>150\text{ }^{\circ}\text{C}$

Auto-ignition temperature:

Does not apply to solids.

Decomposition temperature:

There is no information available on this parameter.

pH:

Mixture is non-soluble (in water).

Kinematic viscosity:

>20,5 mm²/s (40°C, There is no information available on this parameter.)

Solubility:

Insoluble

Partition coefficient n-octanol/water (log value):

Does not apply to mixtures.

Vapour pressure:

There is no information available on this parameter.

Density and/or relative density:

There is no information available on this parameter.

Relative vapour density:

Does not apply to solids.

Particle characteristics:

There is no information available on this parameter.

9.2 Other information

Explosives:

Product is not explosive.

Oxidizing solids:

No

SECTION 10: Stability and reactivity

10.1 Reactivity

The product has not been tested.

10.2 Chemical stability

Stable with proper storage and handling.

10.3 Possibility of hazardous reactions

No dangerous reactions are known.

10.4 Conditions to avoid

See also section 7.

Protect from humidity.

10.5 Incompatible materials

See also section 7.

Avoid contact with strong oxidizing agents.

10.6 Hazardous decomposition products

See also section 5.2

No decomposition when used as directed.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Possibly more information on health effects, see Section 2.1 (classification).

Marine Grease						
Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:						n.d.a.
Acute toxicity, by dermal route:						n.d.a.
Acute toxicity, by inhalation:						n.d.a.
Skin corrosion/irritation:						n.d.a.
Serious eye damage/irritation:						n.d.a.
Respiratory or skin sensitisation:						n.d.a.
Germ cell mutagenicity:						n.d.a.
Carcinogenicity:						n.d.a.
Reproductive toxicity:						n.d.a.
Specific target organ toxicity - single exposure (STOT-SE):						n.d.a.
Specific target organ toxicity - repeated exposure (STOT-RE):						n.d.a.
Aspiration hazard:						n.d.a.
Symptoms:						n.d.a.

11.2. Information on other hazards

Marine Grease						
Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Endocrine disrupting properties:						Does not apply to mixtures.

Page 6 of 9
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II (last amended by Regulation (EU) 2020/878)
Revision date / version: 27.03.2026 / 0020
Replacing version dated / version: 15.03.2024 / 0019
Valid from: 27.03.2026
PDF print date: 27.03.2026
Marine Grease

Other information:						No other relevant information available on adverse effects on health.
--------------------	--	--	--	--	--	---

SECTION 12: Ecological information

Possibly more information on environmental effects, see Section 2.1 (classification).

Marine Grease							
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
12.1. Toxicity to fish:							n.d.a.
12.1. Toxicity to daphnia:							n.d.a.
12.1. Toxicity to algae:							n.d.a.
12.2. Persistence and degradability:							Not readily biodegradable
12.3. Bioaccumulative potential:							n.d.a.
12.4. Mobility in soil:							n.d.a.
12.5. Results of PBT and vPvB assessment							n.d.a.
12.6. Endocrine disrupting properties:							Does not apply to mixtures.
12.7. Other adverse effects:							No information available on other adverse effects on the environment.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

For the substance / mixture / residual amounts

Soaked polluted cloths, paper or other organic materials represent a fire hazard and should be controlled, collected and disposed of.
EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.
Owing to the user's specific conditions for use and disposal, other waste codes may be allocated under certain circumstances. (2014/955/EU)

13 02 05 mineral-based non-chlorinated engine, gear and lubricating oils

Recommendation:

Sewage disposal shall be discouraged.
Pay attention to local and national official regulations.
E.g. dispose at suitable refuse site.
E.g. suitable incineration plant.

For contaminated packing material

Pay attention to local and national official regulations.
Empty container completely.
Uncontaminated packaging can be recycled.
Dispose of packaging that cannot be cleaned in the same manner as the substance.

SECTION 14: Transport information

General statements

Transport by road/by rail (ADR/RID)

14.1. UN number or ID number: Not applicable
14.2. UN proper shipping name: Not applicable
14.3. Transport hazard class(es): Not applicable

14.4. Packing group:	Not applicable
14.5. Environmental hazards:	Not applicable
Tunnel restriction code:	Not applicable
Classification code:	Not applicable
LQ:	Not applicable
Transport category:	Not applicable

Transport by sea (IMDG-code)

14.1. UN number or ID number:	Not applicable
14.2. UN proper shipping name:	Not applicable
14.3. Transport hazard class(es):	Not applicable
14.4. Packing group:	Not applicable
14.5. Environmental hazards:	Not applicable
Marine Pollutant:	Not applicable
EmS:	Not applicable

Transport by air (IATA)

14.1. UN number or ID number:	Not applicable
14.2. UN proper shipping name:	Not applicable
14.3. Transport hazard class(es):	Not applicable
14.4. Packing group:	Not applicable
14.5. Environmental hazards:	Not applicable

14.6. Special precautions for user

Unless specified otherwise, general measures for safe transport must be followed.

14.7. Maritime transport in bulk according to IMO instruments

Non-dangerous material according to Transport Regulations.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Observe restrictions:

General hygiene measures for the handling of chemicals are applicable.

Directive 2010/75/EU (VOC): 0 %

National requirements/regulations on safety and health protection must be applied when using work equipment.

15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

SECTION 16: Other information

Revised sections: 8

Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Not applicable

The following phrases represent the posted Hazard Class and Risk Category Code (GHS/CLP) of the product and the constituents.

Key literature references and sources for data:

Regulation (EC) No 1907/2006 (REACH) and Regulation (EC) No 1272/2008 (CLP) as amended.

Guidelines for the preparation of safety data sheets as amended (ECHA).

Guidelines on labelling and packaging according to the Regulation (EG) Nr. 1272/2008 (CLP) as amended (ECHA).

Safety data sheets for the constituent substances.

ECHA Homepage - Information about chemicals.

GESTIS Substance Database (Germany).

German Environment Agency "Rigoletto" information site on substances that are hazardous to water (Germany).

Page 8 of 9
 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II (last amended by Regulation (EU) 2020/878)
 Revision date / version: 27.03.2026 / 0020
 Replacing version dated / version: 15.03.2024 / 0019
 Valid from: 27.03.2026
 PDF print date: 27.03.2026
 Marine Grease

EU Occupation Exposure Limits Directives 91/322/EEC, 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164, (EU) 2019/1831, each as amended.
 National Lists of Occupational Exposure Limits for each country as amended.
 Regulations on the transport of hazardous goods by road, rail, sea and air (ADR, RID, IMDG, IATA) as amended.

Any abbreviations and acronyms used in this document:

acc., acc. to according, according to
 ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)
 AOX Adsorbable organic halogen compounds
 approx. approximately
 Art., Art. no. Article number
 ASTM ASTM International (American Society for Testing and Materials)
 ATE Acute Toxicity Estimate
 BAM Bundesanstalt für Materialforschung und -prüfung (= Federal Institute for Materials Research and Testing, Germany)
 BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)
 BCF Bioconcentration factor
 BSEF The International Bromine Council
 CAS Chemical Abstracts Service
 CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)
 CMR carcinogenic, mutagenic, reproductive toxic
 DMEL Derived Minimum Effect Level
 DNEL Derived No Effect Level
 DOC Dissolved organic carbon
 e.g. for example (abbreviation of Latin 'exempli gratia'), for instance
 EbCx, EyCx, Eblx (x = 10, 50) Effect Concentration/Level of x % on reduction of the biomass (algae, plants)
 EC European Community
 ECHA European Chemicals Agency
 ECx, ELx (x = 0, 3, 5, 10, 20, 50, 80, 100) Effect Concentration/Level for x % effect
 EEC European Economic Community
 EINECS European Inventory of Existing Commercial Chemical Substances
 ELINCS European List of Notified Chemical Substances
 EN European Norms
 EPA United States Environmental Protection Agency (United States of America)
 ErCx, EμCx, ErLx (x = 10, 50) Effect Concentration/Level of x % on inhibition of the growth rate (algae, plants)
 etc. et cetera
 EU European Union
 EVAL Ethylene-vinyl alcohol copolymer
 Fax. Fax number
 gen. general
 GHS Globally Harmonized System of Classification and Labelling of Chemicals
 GWP Global warming potential
 Koc Adsorption coefficient of organic carbon in the soil
 Kow octanol-water partition coefficient
 IARC International Agency for Research on Cancer
 IATA International Air Transport Association
 IBC (Code) International Bulk Chemical (Code)
 IMDG-code International Maritime Code for Dangerous Goods
 incl. including, inclusive
 IUCLID International Uniform Chemical Information Database
 IUPAC International Union for Pure Applied Chemistry
 LC50 Lethal Concentration to 50 % of a test population
 LD50 Lethal Dose to 50% of a test population (Median Lethal Dose)
 Log Koc Logarithm of adsorption coefficient of organic carbon in the soil
 Log Kow, Log Pow Logarithm of octanol-water partition coefficient
 LQ Limited Quantities
 MARPOL International Convention for the Prevention of Marine Pollution from Ships
 mg/kg bw mg/kg body weight
 mg/kg bw/d, mg/kg bw/day mg/kg body weight/day
 mg/kg dw mg/kg dry weight
 mg/kg ww mg/kg wet weight

n.a. not applicable

n.av. not available

n.c. not checked

n.d.a. no data available

NIOSH National Institute for Occupational Safety and Health (USA)

NLP No-longer-Polymer

NOEC, NOEL No Observed Effect Concentration/Level

OECD Organisation for Economic Co-operation and Development

org. organic

OSHA Occupational Safety and Health Administration (USA)

PBT Persistent, bioaccumulative and toxic

PE Polyethylene

PMT Persistent, mobile and toxic

PNEC Predicted No Effect Concentration

ppm parts per million

PVC Polyvinylchloride

REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)

REACH-IT List-No. 6/7/8/9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.

RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)

SVHC Substances of Very High Concern

Tel. Telephone

TOC Total organic carbon

UN RTDG United Nations Recommendations on the Transport of Dangerous Goods

VOC Volatile organic compounds

vPvB Very persistent and very bioaccumulative

vPvM Very persistent and very mobile

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge.

No responsibility.

These statements were made by:

Chemical Check GmbH, Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.