

# MAGLITE®

## ML50LX™

### Packaging Options



Blister pack



Chipboard box

### Features & Benefits



Activity-Based function sets



QuickClick® electronic switch



QuickFocus™



IPX4 Water Resistant

### Available Colors



Black Foliage Green Urban Gray

With the familiar “QuickClick™” system users can, within the “General” function set, choose Full Power (maximum Lumens): Low Power (up to 113 Lumens: 2-Cell); or Eco Mode - a super power saving mode that yields up to 23 Lumens (2-Cell) with greatly extended run-time.

There are three additional function sets – Outdoor; Law Enforcement; and Military – each offering a different set of functions invoked in a different sequence, for quickest access to the functions the particular user prefers.

The IMPROVED, faster-handling “Quick Focus™” system now adjusts from spot to flood with about a ¼ turn of the head.

### Function Sets

Function Set	1 GENERAL (Default)	2 OUTDOOR	3 LAW ENFORCEMENT	4 TACTICAL
1 CLICK	Full Power	Full Power	Momentary	Momentary
2 CLICKS	Low Power	Low Power	Full Power	Full Power
3 CLICKS	Eco	Strobe	Eco	Strobe



- Aggressive Knurled Design
- Stealth Matte Finish

## TECHNICAL SPECIFICATIONS



### 2-Cell C

- Type - **Mid Size**
- Lumens - **490 lm**
- Beam Distance - **299m**
- Peak Beam Intensity - **22400cd**
- Barrel Diameter - **1.2 in. / 30.48 mm**
- Batteries - **(Alkaline) Not Included**
- Weight With Batteries - **12.72 oz. / 360.61g**
- Water-Resistant - **Yes**
- Drop Resistance - **1m**
- Technology - **LED**
- Length - **8.184 in. / 207.87 mm**
- Run Time, High/Low/Eco - **15h/29h/112h**
- Head Diameter - **1.977 in. / 50.22 mm**
- Rechargeable - **No**
- Blister Size - **13 H x 5 W x 2 D in.**
- Chipboard Box Size - **8.34 H x 1.97 W x 1.97 D in.**



### 3-Cell C

- Type - **Mid Size**
- Lumens - **611 lm**
- Beam Distance - **339m**
- Peak Beam Intensity - **28760cd**
- Barrel Diameter - **1.2 in. / 30.48 mm**
- Batteries - **(Alkaline) Not Included**
- Weight With Batteries - **16 oz. / 453.59g**
- Water-Resistant - **Yes**
- Drop Resistance - **1m**
- Technology - **LED**
- Length - **10.154 in. / 257.912 mm**
- Run Time, High/Low/Eco - **16h/42h/153h**
- Head Diameter - **1.977 in. / 50.22 mm**
- Rechargeable - **No**
- Blister Size - **13 H x 5 W x 2 D in.**
- Chipboard Box Size - **10.28 H x 1.97 W x 1.97 D in.**

**MAGLITE®** MAG INSTRUMENT, INC. • 2001 South Hellman Ave., Ontario, CA 91761  
909-947-1006 • 800-289-6241 • www.maglite.com • email: salesdesk@magmail.com

\* Under Mag Instrument's Continuous Product Improvement strategy, we do make in-line changes to existing products that can impact performance. The ANSI test results shown here are current as this spec sheet goes to press. Consult product packaging/labeling for any updated performance figures.

The Mag-Lite® ML50LX™ flashlight is covered by U.S. Patent Nos. 8,210,710; 8,240,874; 8,395,066; 8,482,209; 8,507,819 and 9,255,696. The LED Module is covered by U.S. Patent No. D625,847. Other patents pending on the flashlight and LED Module. Flashlight designed and manufactured in the U.S.A. Mag Instrument's factory is located in Ontario, California. Includes some imported components. The distinctive shapes, styles and overall appearances of all Mag® flashlights, and the circumferential inscription on the heads of all Mag® flashlights, are trademarks of Mag Instrument. The circumferential inscription on the head of a flashlight signifies that it is an original Mag® flashlight and part of the Mag® family of flashlights. U.S. Trademark Registrations for the circumferential inscription and the shape, style and overall appearance of Mag® flashlights include Reg. Nos. 1,808,998, 2,074,795, 2,687,693, 2,745,460, 2,765,978 and 2,765,979. The ornamental patterns of knurling on Maglite® flashlights are trademarks of Mag Instrument (see U.S. Trademark Reg. No. 3,839,734). ©2017 MAG INSTRUMENT, INC.

