


Datasheet

Manufacturer Part No.: T24C009 ... T24C012

Heat shrink solder seal sleeves Ø 0.25 ... 6 mm² bulk set 50 pcs



The hot-melting inner adhesive seals watertight when overlapped correctly - the solder ring connects the two conductors during the shrinking and melting process! Advantageous with transparent design is that you can see the wrapped object.

The application is very simple: Strip the cable and insert it on both sides into the connector until the stripped cable ends overlap under the solder ring, or twist. Even heating in the melting temperature at the solder until it is melted - optimally with a hot air gun or a hot air blower - done.

The maximum current is limited by the conductor cross-section of the cable used, its conductor material and the quality of the solder joint.

Technical data: Cross section: 0.25 ... 6 mm² • Shrink ratio: 2:1 • IP-class: IP67 (Correct application required) • Temp.-range: -55 ... 125 °C • Melt temp at solder: appx. 160 °C • Voltage resistance: max. 600 V.

Part No.	Description	Color	Cross section	Diameter	Length	EAN / GTIN	Content
T24C009	Heat shrink solder seal sleeve 0.25 - 0.34 mm ²	White	0.25 ... 0.34 mm ²	1.7 mm	26 mm	4260732286363	50 pcs
T24C010	Heat shrink solder seal sleeve 0.5 - 1 mm ²	Red	0.5 ... 1.0 mm ²	2.7 mm	40 mm	4260732286370	50 pcs
T24C011	Heat shrink solder seal sleeve 1.5 - 2.5 mm ²	Blue	1.5 ... 2.5 mm ²	4.5 mm	40 mm	4260732286387	50 pcs
T24C012	Heat shrink solder seal sleeve 4 - 6 mm ²	Yellow	4.0 ... 6.0 mm ²	6.0 mm	40 mm	4260732286394	50 pcs

Notice: Max. current limited by cable-diameter, cable-material and quality of the soldering joint!

Connection only by qualified electricians. We assume no liability or warranty in case of incorrect application.