

ICP582930PR-01

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V Safety Circuit, Connector

Specifications

Renata Type ICP582930
IEC Designation ICP073032
Part Number 100650
Contact method Wire AWG30

Safety Circuit Yes

Nominal Voltage 3.7 V Nominal Capacity 450 mAh Minimum Capacity 430 mAh

(0.2C cut off 3.0 V at

20℃)

Internal Impedance $< 200 \text{ m}\Omega / 50\% \text{ SOC}$

Thickness (t) Max 6.2 mm
Lenghth (I Max 32.0 mm
Width (w) Max 29.5 mm
Weight ~ 9.1 q

....g... 5.1 (

Charging Characteristic CC/CV – Constant Current / Constant Voltage

Voltage 4.2 V CV

Current Normal 0.5 C CC - 225 mAMax. Charging Current 1.0 C CC - 450 mATemperature at Charging $0 \text{ °C} \dots 45 \text{ °C}$

Discharge Characteristic

Cut off Voltage 3.0 V

Max Discharge Current 2.0 C – 900 mA (for non continues discharge)

1.0 C – 450 mA (for continues discharge)

Temperature during Discharge -20 ℃ ... 60 ℃

Cycle Life at Room Temperature > 80% of minimum capacity after 500 cycles (0.5 C

charge, 0.5 C discharge)


Storage Temperature -20 °C ... 45 °C

(0 °C ... 30 °C recommended in case of storage for

more than 3 months)

Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.





Rev. ICP ICP582930 - 11.01