

IE-SWM-SL02-2GESFP+**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Features of SubstationLine managed switch series

The SubstationLine includes Ethernet switches complying with the IEC 61850-3 and IEEE 1613 standards, making them robust enough for operation in harsh environments. The family includes variants for mounting on DIN rails and in 19" racks.

All products have a redundant power supply to ensure reliability in critical environments. The new family ranges from managed Fast Ethernet switches to 10-Gigabit Ethernet products with all the necessary features to operate according to the most demanding requirements.

- DIN-rail and 19" rack variants
- IEC 61850-3 and IEEE 1613 compliance
- PRP/HSR support according to Clause 4/Clause 5 of IEC 62439-3
- MMS server based on bridge model defined in IEC 61850-90-4
- Redundant power supply modules in all models
- Wide operating temperature range of -40°C up to 85°C
- Modular switch version with high flexibility in number and type of ports
- Fast/Gigabit/10-Gigabit interfaces
- Layer 3 models for hardware supported routing between up to 28 IP-subnets

General ordering data

Version	Media interface module for modular switch, Gigabit Ethernet/10-Gigabit Ethernet, Number of ports: 2x 1000BaseSFP/10GBaseSFP+ slot, -40 °C...60 °C
Order No.	2779210000
Type	IE-SWM-SL02-2GESFP+
GTIN (EAN)	4064675048572
Qty.	1 items

IE-SWM-SL02-2GESFP+

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	136 mm	Depth (inches)	5.3543 inch
Height	40.7 mm	Height (inches)	1.6024 inch
Width	99 mm	Width (inches)	3.8976 inch
Net weight	348 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...60 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	Lead monoxide 1317-36-8

Environmental conditions

Operating temperature, max.	60 °C	
Operating temperature, min.	-40 °C	
Humidity	5 to 95 % (non-condensing)	
Storage temperature, max.	85 °C	
Storage temperature, min.	-40 °C	
Operating altitude	Altitude, max.	2000 m
	Note	in acc. with UL
	Altitude, max.	6000 m
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads

Guarantee

Time interval	5 years
---------------	---------

Interfaces

Fibre-optic ports	1000BaseSFP/10GBaseSFP + slot	Number of ports	2x 1000BaseSFP/10GBaseSFP + slot
-------------------	-------------------------------	-----------------	-------------------------------------

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	3814097 h

IE-SWM-SL02-2GESFP+

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Power supply

Supply voltage	via Ethernet switch
----------------	---------------------

Technical data

Housing main material	Metal	Type of mounting	Insert in module slot M4
Speed	Gigabit Ethernet/10-Gigabit Ethernet		

Classifications

ETIM 6.0	EC000309	ETIM 7.0	EC000309
ETIM 8.0	EC000309	ETIM 9.0	EC000309
ETIM 10.0	EC000309	ECLASS 9.1	19-17-03-90
ECLASS 10.0	19-17-04-90	ECLASS 11.0	19-17-03-03
ECLASS 12.0	19-17-03-03	ECLASS 13.0	19-17-03-03
ECLASS 14.0	19-17-03-03	ECLASS 15.0	19-17-03-03

IE-SWM-SL02-2GESFP+

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

SFP transceiver (for use with switches of Eco-, Advanced-, Substation and BasicLine series B)



Features of SFP-Transceiver series

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Type	IE-SFP-1GE-MM-05	Version
Order No.	2682480000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.5 km, -40
GTIN (EAN)	4050118692235	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-MM-2	Version
Order No.	2682490000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, -40
GTIN (EAN)	4050118692228	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10	Version
Order No.	2682500000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, -40
GTIN (EAN)	4050118692211	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-40	Version
Order No.	2682510000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40
GTIN (EAN)	4050118692204	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10-BIDI-T...	Version
Order No.	2682520000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692198	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10-BIDI-T...	Version
Order No.	2682530000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692181	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-20-BIDI-T...	Version
Order No.	2682540000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692174	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-20-BIDI-T...	Version
Order No.	2682550000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692167	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-10GE-MM-03	Version
Order No.	2779110000	SFP+ transceiver, 10 Gbps, Multimode, LC-Duplex, 0.3 km, -40 °C...85
GTIN (EAN)	4064675048473	°C
Qty.	1 ST	
Type	IE-SFP-10GE-SM-20	Version
Order No.	2779120000	SFP+ transceiver, 10 Gbps, Singlemode, LC-Duplex, 20 km, -40
GTIN (EAN)	4064675048480	°C...85 °C
Qty.	1 ST	

IE-SWM-SL02-2GESFP+

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	IE-SFP-10GE-SM-40	Version	
Order No.	2779130000	SFP+ transceiver, 10 Gbps, Singlemode, LC-Duplex, 40 km, -40	
GTIN (EAN)	4064675048497	°C...85 °C	
Qty.	1 ST		