


3200pcs Cable-ferrules-assortment


The assortment consists of uninsulated and insulated wire end ferrules in a practical transparent assortment box. The assortment includes various wire end ferrules from 0.5 mm² to 10 mm² for fine and finest wires. Simple insulation for splice-free cable entry. Temperature resistant up to 75/120°C. Galvanic tinned for protection against corrosion. Material: copper and plastic, surface finishing: tinned.



Section	Contents	pcs
1	Non-Insulated Cable Ferrules, 0.5mm ² x 8mm	700
	Non-Insulated Cable Ferrules, 0.75mm ² x 8mm	700
	Non-Insulated Cable Ferrules, 1.0mm ² x 6mm	700
2	Non-Insulated Cable Ferrules, 1.5mm ² x 8mm	700
	Insulated Cable Ferrules, 0.5mm ² x 8mm	60
3	Insulated Cable Ferrules, 0.75mm ² x 8mm	60
	Insulated Cable Ferrules, 6.0mm ² x 12mm	30
4	Insulated Cable Ferrules, 1.0mm ² x 8mm	60
	Insulated Cable Ferrules, 1.5mm ² x 8mm	60
5	Insulated Cable Ferrules, 10mm ² x 12mm	30
	Insulated Cable Ferrules, 4.0mm ² x 9mm	50
6	Insulated Cable Ferrules, 2.5mm ² x 8mm	50




Non-Insulated cable ferrules



Material: Tinned Copper
Operating Voltage: 600V max.
Operating Temperature: 120°C max.

Wire Range (mm ²)	L(mm)	D(ømm)	D1(ømm)	D2(ømm)
0.5	8.0	3.1	1.0	1.3
0.75	8.0	2.3	1.2	1.5
1.0	6.0	2.5	1.4	1.7
1.5	8.0	2.8	1.7	2.0

Insulated cable ferrules



Insulator Material: Vinyl
Terminal Material: Tinned Copper
Operating Voltage: 600V max.
Operating Temperature: 75°C max.

Wire Range (mm ²)	L(mm)	L1(mm)	L2(mm)	D(ømm)	D1(ømm)	D2(ømm)	code (DE)
0.5	14.0	6.0	8.0	2.6	1.0	1.3	Orange
0.75	14.0	6.0	8.0	2.8	1.2	1.5	White
1.0	14.0	6.0	8.0	3.0	1.4	1.7	Yellow
1.5	14.0	6.0	8.0	3.5	1.7	2.0	Red
2.5	14.0	6.0	8.0	4.2	2.2	2.6	Blue
4	18.0	9.0	9.0	4.8	2.8	3.2	Grey
6	20.0	8.0	12.0	6.3	3.5	3.9	Black
10	22.0	10.0	12.0	7.6	4.5	4.9	Ivory

Datasheet

Manufacturer Part No.: T24C034

Self Adjusting Wire-End Ferrule Crimping Pliers, Range 0.25...10 mm² (AWG 23-7)



This crimping tool is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs. The crimping tool is optimally matched to the field of application and has an automatic adjustment to the sleeve diameters between 0.25 and 10 sqmm. The square crimping claw ensures a safe crimping process, the ergonomic handle fits well in the hand and allows comfortable working. The pliers have an adjustment option for fine adjustment of the compressive force and a quick locking safety lock.

Technical Specifications

Four-mandrel press claw • Automatic adjustment • Fine adjustment ratchet pressure • Quick release safety lock • Ergonomic handle • Range from 0.25 - 10 mm² (AWG 23 - 7) • Weight: 363 g.