




Capabilities

The following table outlines the capabilities of this GENIE device:

Type	CORE
Signals	
Pins	20
Analogue inputs	4
ADC resolution	8 bits
Digital inputs	8
Digital outputs	9
Features	
Parallel processing	Yes
Plug and play	Yes
Debug live	Yes
Device control	Yes
Sensor calibration	Yes
Polyphonic music	Yes
PWM output	1
Servo motor control	0
Infra-red control	Yes
Looping	Yes
Events	Yes
Interrupts	Yes
1-second clock	Yes
Programming	
Memory	160
Variables	10 (A-J)
EEPROM locations	16
Flowchart start limit	2
Subroutine limit	No limit
Call stack limit	16
Electrical	
PICmicro® device	16F677
Power supply	2.1-5.5V
Pin current limit	25mA
Total current limit	90mA

Component

The GENIE C20 microcontroller has 20 legs (known as pins) and these are used as follows (a simplified view is also shown):



Pin	Description
1	Power supply voltage (2.1-5.5V only)
2	Programming input (PR)
3	Analogue input A7 or digital input D7
4	Digital input D6
5	Digital input D5
6	Digital input D4
7	Analogue input A3 or digital input D3
8	Analogue input A2 or digital input D2
9	Analogue input A1 or digital input D1
10	Digital input D0
11	Digital output Q7
12	Digital output Q6
13	Digital output Q5
14	Digital output Q4
15	Digital output Q3
16	Digital output Q2
17	Digital output Q1
18	Digital output Q0
19	Status output (ST)
20	Ground (zero volt) supply voltage

The required circuit for a GENIE C20 is shown below. It includes a download socket and two resistors.

