


KLIPPON COPL 165609**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
-
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Version	Klippon POK (polyester empty enclosure), Earthing plate, Miscellaneous, Height: 60.5 mm, Width: 656 mm, Depth: 0.8 mm, Basic material: Brass, polished, untreated
Order No.	1391020000
Type	KLIPPON COPL 165609
GTIN (EAN)	4050118191134
Qty.	5 items

KLIPPON COPL 165609

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.8 mm	Depth (inches)	0.0315 inch
Height	60.5 mm	Height (inches)	2.3819 inch
Width	656 mm	Width (inches)	25.8267 inch
Wall thickness, min.	0.8 mm	Wall thickness, max.	0.8 mm
Net weight	50 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Material thickness	0.8 mm	Surface finish	polished, untreated
Basic material	Brass		

Classifications

ETIM 6.0	EC002623	ETIM 7.0	EC002623
ETIM 8.0	EC002623	ETIM 9.0	EC002623
ETIM 10.0	EC002623	ECLASS 9.0	27-18-28-14
ECLASS 9.1	27-18-92-64	ECLASS 10.0	27-18-28-14
ECLASS 11.0	27-18-28-14	ECLASS 12.0	27-18-28-14
ECLASS 13.0	27-18-28-14	ECLASS 14.0	27-18-28-14
ECLASS 15.0	27-18-28-14		