




Dimensions

Positions	A	B	C	E	F
15	39.20	33.30	25.25	19.39	27.70

Dimensions

Positions	A ± 0.15	B ± 0.10	D ± 0.13	E ± 0.08	F ± 0.10
15	39.20	33.30	24.70	19.39	27.70

NOTES:

MATERIAL

1. Insulator Material: Glass-filled thermoplastic PBT, UL94V-0
2. Contact Material: Brass or Phosphor Bronze
3. Shell : Steel, 100 μ " Tin Over 50 μ " min Copper
4. Clinch Nut : Brass, Nickel Plated
5. Contact plating : Gold flash full gold & selective 15 μ " Au

ELECTRICAL

1. Current Rating : 3AMP
2. Voltage Rating : 250V AC/rms 60Hz
3. Contact Resistance: 20m Ω
4. Insulation Resistance: 1000M Ω min at 500 VDC
5. Withstand Voltage: 1000V AC/rms 60Hz for 1 minute

ENVIRONMENTAL

1. Temperature Range: -20°C~+105°C

UL No. E198287

NOTES:

MATERIAL

1. Insulator Material: Glass-filled thermoplastic PBT, UL94V-0, Gray
2. Contact Material: Copper alloy
3. Shell : Steel, 100 μ " Tin Over 50 μ " min Copper
4. Clinch Nut : Brass, Nickel Plated
5. Contact plating : Gold flash full gold

ELECTRICAL

1. Current Rating : 3AMP
2. Voltage Rating : 250V AC/rms 60Hz
3. Contact Resistance: 20m Ω Max at 1 AMP DC
4. Insulation Resistance: 1000M Ω at 500 VDC
5. Withstand Voltage: 1000V AC/rms 60Hz for 1 minute
6. OPERATING TEMPERATURE: -20°C~+105°C

UL No. E198287

RoHS compliant

Unit:mm