

IE-SFP-1GLHXLC-T**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

- Supports DDM (Digital Diagnostic Monitoring)
- IEEE 802.3z compliant (Gigabit Ethernet SFPs)
- IEEE 802.3u compliant (Fast Ethernet SFPs)
- Symmetric LVPECL I/Os (Gigabit Ethernet SFPs)
- Symmetric PECL I/Os (Fast Ethernet SFPs)
- TTL signal detection indicator
- Pluggable in operation (hot pluggable)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Basic-, Value- and PremiumLine

General ordering data

Version	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40 °C...85 °C
Order No.	1286730000
Type	IE-SFP-1GLHXLC-T
GTIN (EAN)	4050118077728
Qty.	1 items

IE-SFP-1GLHXLC-T

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E230683

Dimensions and weights

Net weight 25 g

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 7cl

REACH SVHC No SVHC above 0.1 wt%

EMC conformity and approvals

EMC standards	EN 55032, EN 55035	Ship use	DNV
Safety standard	UL 62368-1, EN 62368-1, EN 60825-1		

Environmental conditions

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Humidity	5 to 95 % (non-condensing)	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate 1000 Mbps

Digital diagnostic monitor function (DDM) Supported

Transceiver type Singlemode

Connector type LC-Duplex

Transmission distance, typ. 40 km

Wavelength	typ.	1310 nm
	Wavelength	TX
	min.	1280 nm
	max.	1340 nm
	Wavelength	RX
	min.	1260 nm
Receive power	max.	1610 nm
	min.	-24 dBm
Transmission power	max.	-1 dBm
	min.	-4 dBm

IE-SFP-1GLHXLC-T

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

	max.	3 dBm
Link-budget	20 dB	
Note	When connecting a single-mode fiber transceiver over a short distance, we recommend using an attenuator to prevent the transceiver from being damaged by excessive optical power.	

Guarantee

Time interval	3 years
---------------	---------

Interfaces

Ethernet ports	1	Plug-in connector	Duplex-LC
----------------	---	-------------------	-----------

Power supply

Supply voltage	3.3 V (via Ethernet switch)
----------------	-----------------------------

Technical data

Type of mounting	Insert in SFP slot
------------------	--------------------

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC003628	ETIM 9.0	EC003628
ETIM 10.0	EC003628	ECLASS 9.1	27-44-02-92
ECLASS 10.0	27-44-02-92	ECLASS 11.0	19-17-03-03
ECLASS 12.0	19-17-03-03	ECLASS 13.0	19-17-03-03
ECLASS 14.0	19-17-03-03	ECLASS 15.0	19-17-03-03

IE-SFP-1GLHXLC-T**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****LC-Duplex**

Mounting rail outlet, LC duplex junction design according to IEC 61754-20

General ordering data

Type	IE-TO-LCD-SM	Version	
Order No.	8947020000	Mounting rail outlet, fibre-optic, LC Duplex, Singlemode, IP20	
GTIN (EAN)	4032248735037		
Qty.	10 ST		