



Weidmüller Interface GmbH & Co. KG

1

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Product image Similar to illustration





The comprehensive range of stud terminals ensures secure connections for all power transmission applications. Connections range from 10 mm² to 300 mm². The connectors are attached to the threaded pins using crimped cable lugs and each connection is secured by tightening the hexagon nut. Stud terminals with threaded pins from M5 to M16 can be used according to the wire cross-section.

General ordering data

Version	Bolt-type screw terminals, Feed-through terminal, Rated cross-section: 16 mm², Threaded stud con- nection
Order No.	<u>1319040000</u>
Туре	WF 5/32
GTIN (EAN)	4050118320084
Qty.	25 items





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals			
Approvals	(€		
ROHS	Conform		
Dimensions and weights			
Depth	61 mm	Depth (inches)	2.4016 inch
Height	67 mm	Height (inches)	2.6378 inch
Width	13 mm	Width (inches)	0.5118 inch
Net weight	19.15 g	width (menes)	0.5110 men
Temperatures			
Storage temperature	-25 °C55 °C	Ambient temperature	-5 °C40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
Environmental Product Comp	oliance		
RoHS Compliance Status	Compliant without exemptio	n .	
REACH SVHC	No SVHC above 0.1 wt%	11	
ILAGI OVIIC	TWO SYTTE ADOVE U. I WI70		
Material data			
Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		
System specifications			
- , o to in opposition to in o			
Version	Single-stud terminals	End cover plate required	No
Number of potentials	1	Number of levels	1
Number of clamping points per level	1	Levels cross-connected internally	No
PE connection	No	Mounting rail	TS 32
Additional technical data			
Explosion-tested version	No	Type of mounting	Snap-on
Conductors for clamping (rat	ed connection)		1
Cable lug to DIN 46234	0.116 mm ²	Cable lug to DIN 46235	610 mm ²
Wire connection cross section AWG,	AWG 4	Connection direction	on side
max.	4.01	T: 1	0.11
Tightening torque, max.	4 Nm	Tightening torque, min.	2 Nm
Type of connection	Threaded stud connection	Number of connections	1
Clamping range, max.	16 mm ²	Clamping range, min.	0.1 mm ²
Wire connection cross section AWG, min.	AWG 27	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.41 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN	0.41 mm ²	Wire connection cross section, finely stranded, max.	16 mm²
46228/1, min.			

Creation date 02.10.2025 09:43:07 MEZ

Wire connection cross section, finely

stranded, min.

Catalogue status / Drawings 2

Connection cross-section, stranded,

16 mm²

0.41 mm²





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Connection cross-section, stranded, min. 0.41 mm ²		Stud size for spade connection	M 5
Wire connection cross-section, solid core, max.	16 mm²	Wire connection cross-section, solid core, min.	0.41 mm ²
Connection cross-section, finely stranded, min.	0.41 mm ²	2 x cable lugs DIN 46 235	610 mm²
2 x cable lugs DIN 46 234	0.1 to 16 mm ²		

General

Wire connection cross section AWG,	AWG 4	Wire connection cross section AWG,	AWG 27
max.		min.	
Standards	IEC 60947-7-1	Mounting rail	TS 32

Rating data

Rated cross-section	16 mm ²	Rated voltage	1000 V
Rated DC voltage	1000 V	Nominal current	76 A
Current at maximum wires	76 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	0.42 mΩ	Rated impulse withstand voltage	8 kV
Power loss in accordance with IEC 60947-7-x	2.43 W		

Classifications

	'		
ETIM 6.0	EC000897	ETIM 7.0	EC000897
ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 9.0	27-14-11-20
ECLASS 9.1	27-14-11-20	ECLASS 10.0	27-14-11-20
ECLASS 11.0	27-14-11-20	ECLASS 12.0	27-14-11-20
ECLASS 13.0	27-25-01-01	ECLASS 14.0	27-25-01-01
ECLASS 15.0	27-25-01-01		

Data sheet





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Standard



Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Туре	WQL 2 WF5	Version
Order No.	<u>1812710000</u>	Bolt-type screw terminals, Cross-connector, Number of poles: 2
GTIN (EAN)	4032248404568	
Qty.	5 ST	
Туре	WQL 3 WF5	Version
Type Order No.	WQL 3 WF5 1812740000	Version Bolt-type screw terminals, Cross-connector, Number of poles: 3

WF / WFF-Series



A partition plate is used for the optical separation of circuits or used for electrical isolation from neighbouring cross-connectors. In contrast to the end plate, the contour can be larger than the adjacent terminal blocks. However, it should not be smaller, as otherwise the required clearance and creepage distances within the application can no longer be maintained.

General ordering data

Туре	WTW WF6-WF12	Version
Order No.	<u>1781240000</u>	Bolt-type screw terminals, Partition plate, dark beige, 2.5 mm
GTIN (EAN)	4032248241156	
Qty.	20 ST	
Type	WTW WF6 2300	Version
Type Order No.	WTW WF6 2300 1781230000	Version Bolt-type screw terminals, Partition plate, grey, 2 mm

Creation date 02.10.2025 09:43:07 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

W-Series



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Type WEW 35/2
Order No. 1061200000
GTIN (EAN) 4008190030230
Oty. 50 ST

Version

End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 $^{\circ}\text{C}$

Cover profiles



Cover profiles provide protection against external impact on functional areas of the terminal blocks or in combination with our support brackets for the entire terminal strip. They provide protection against electric shock caused by accidental contact with live parts due to operation or faults.

General ordering data

Туре	ADP WF6/WF8	Version
Order No.	<u>1780930000</u>	Bolt-type screw terminals, Cover profile, Transparent, 1000 mm
GTIN (EAN)	4032248241248	
Qty.	1 M	
Type	HA ADP WF6/WF10	Version
Type Order No.	HA ADP WF6/WF10 1781050000	Version Bolt-type screw terminals, Cover profile, dark beige, 2.2 mm
	· ·	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Туре	DEK 5/6 MC NE WS	Version
Order No.	<u>1609820000</u>	Dekafix, Terminal marker, 5 x 6 mm, Pitch in mm (P): 6.00
GTIN (EAN)	4008190203436	Weidmueller, white
Qty.	1000 ST	
Туре	WS 15/5 MC NE WS	Version
Type Order No.	WS 15/5 MC NE WS 1609880000	Version WS, Terminal marker, 15 x 5 mm, Pitch in mm (P): 5.00 Weidmueller,
	· ·	

Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snaped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

General ordering data

Туре	BZT 1 WS 10/5	Version
Order No.	<u>1805490000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 ST	
Туре	BZT 1 ZA WS 10/5	Version
Order No.	<u>1805520000</u>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 ST	

Creation date 02.10.2025 09:43:07 MEZ

Data sheet

WF 5/32



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Accessories

DEK 5/6



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- · Firm hold and durable printing
- · Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

	- · · · · · · · · · · · · · · · · · · ·	
Туре	DEK 5/6 MM WS	Version
Order No.	2007120000	Dekafix, Terminal marker, 5 x 6 mm, Weidmueller, white
GTIN (EAN)	4050118392104	
Qty.	600 ST	