


LED-Signalleuchte SWBU14 Ø14mm IP67 LED-Signal Indicator SWBU14 Ø14mm IP67



Spezifikation

LED-Signalleuchte mit ultraheller LED und kombiniertem Innen- und Außenreflektor mit Einweg-Gleichrichtung. Schutzart IP67. Einbau-Ø14mm, Schraubbefestigung, Metallgehäuse glanzverchromt, Frontplatteneinbau. Lieferumfang: Befestigungsmaterial mit einschließlich Außendichtring, sowie zusätzliche Berührungsschutzhülse bei 230V-Typen.

Einbau-Öffnung: Ø14+0,2mm

Anschluss: Flachstecker 2,8x0,8 mm

Materialien

Teil	Material
Gehäuse	Messing verchromt
Dichtring / Dichtscheibe	NBR 70
Isolierteil	Polycarbonat
Reflektor	Polycarbonat transparent
Mutter	Messing vernickelt
Unterlegling	FE vernickelt

Betriebstemperatur	-40/+70°C
Lagertemperatur	-40/+100°C

Optionen

Gehäuse schwarzchrom
Gehäuse mattchrom

Specification

LED indicator with ultra bright LED and combined inside and outside reflector with half-wave rectification. Protection IP67. Mounting-Ø14 mm, screw fastening, metal housing in chromium plated, front panel installation.

Scope of delivery: mounting material with seal ring and a shock-protection sleeve for 230V-types.

Mounting-hole: Ø14+0,2mm

Connection: Tab terminal 2.8x0.8 mm

Material

Part	Material
Housing	Brass chromium plated
seal ring / sealing disk	NBR 70
Insulating part	Polycarbonate
Reflector	Polycarbonate transparent
Nut	Brass nickel plated
Washer	FE nickel plated

Operation Temperature	-40/+70°C
Storage Temperature	-40/+100°C

Options

Housing black chromium plated
Housing frosted chromium plated

Artikel/ Part		Artikel-Text		Part-Text			
Spannung Voltage	Farbe Color	Lichtstärke Luminous intensity	Vollwinkel Viewing Angle	Lichtstrom luminous flux	Strom Current	Leistung Power	Lebensdauer live-time
SWBU14022 LED-Leuchte EØ14 ROT IRgc 12VAD							
12 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWBU14024 LED-Leuchte EØ14 ROT IRgc 24VAD							
24 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWBU14027 LED-Leuchte EØ14 ROT IRgc 130VA							
130 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWBU14028 SigLeu EØ14 ROT 230VA IRgc							
230 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWBU14122 SigLeuØ14 GELB 12VAD IRgc							
12 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWBU14124 SigLeuØ14 GELB 24VAD IRgc							
24 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWBU14127 SigLeu EØ14 GELB 130VA IRgc							
130 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWBU14128 SigLeu EØ14 GELB 230VA IRgc							
230 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWBU14422 LED-Leuchte EØ14 BLAU IRgc 12VAD							
12 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWBU14424 LED-Leuchte EØ14 BLAU IRgc 24VAD							
24 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWBU14427 SigLeu EØ14 BLAU 130VA IRgc							
130 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWBU14428 SigLeu EØ14 BLAU 230VA IRgc							
230 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWBU14622 LED-Leuchte EØ14 WEISS IRgc12VAD							
12 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWBU14624 LED-Leuchte EØ14 WEISS IRgc24VAD							
24 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWBU14627 SigLeu EØ14 WEISS 130VA IRgc							
130 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWBU14628 SigLeu EØ14 WEISS 230VA IRgc							
230 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWBU14722 LED-Leuchte EØ14 UG IRgc 12VAD							
12 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWBU14724 LED-Leuchte EØ14 UG IRgc 24VAD							
24 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWBU14727 SigLeu EØ14 UGRÜN 130VA IRgc							
130 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h

Artikel/ Part		Artikel-Text		Part-Text			
Spannung Voltage	Farbe Color	Lichtstärke Luminous intensity	Vollwinkel Viewing Angle	Lichtstrom luminous flux	Strom Current	Leistung Power	Lebensdauer live-time
SWBU14728 SigLeu EØ14 UGRÜN 230VA IRgc							
230 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h

Layout FPI

Technische Änderungen vorbehalten. Datenblatt unterliegt nicht dem Änderungsdienst.
Die angegebenen technischen Daten sind typische Durchschnittswerte.

Wir achten bei der Entwicklung und Herstellung und beim Energieverbrauch unserer Produkte auf einen möglichst geringen Einsatz von Ressourcen.
Bitte prüfen Sie, ob es unbedingt erforderlich ist, das gesamte Dokument zu Drucken. So schonen Sie Ressourcen und unsere Umwelt.

Specifications are subject to change without notice.

The technical data are typical figures

*We care for environment when producing and manufacturing our products.
Also we care for a low power consumption and a low consumption of resources.
Please consider environmental responsibility before printing this e-mail*