

LED-Signalleuchte SWDU14 Ø14mm IP67 LED-Signal Indicator SWDU14 Ø14mm IP67



Spezifikation

LED-Signalleuchte mit ultraheller LED und kombiniertem Innen- und Außenreflektor mit Einweg-Gleichrichtung. Schutzart IP67. Einbau-Ø14mm, Schraubbefestigung, Metallgehäuse schwarzverchromt, Frontplatteneinbau.

Lieferumfang: Befestigungsmaterial mit einschließlich Außendichtring, sowie zusätzliche Berührungsschutzhülse bei 230V-Typen.

Einbau-Öffnung: Ø14+0,2mm

Anschluss: Flachstecker 2,8x0,8 mm

Specification

LED indicator with ultra bright LED and combined inside and outside reflector with half-wave rectification. Protection IP67.

Mounting-Ø14 mm, screw fastening, metal housing in black chromium, front panel installation.

Scope of delivery: mounting material with seal ring and a shock-protection sleeve for 230V-types.

Mounting-hole: Ø14+0,2mm

Connection: Tab terminal 2.8x0.8 mm

Materialien

Teil	Material
Gehäuse	Messing verchromt
Dichtring / Dichtscheibe	NBR 70
Isolierteil	Polycarbonat
Reflektor	Polycarbonat transparent
Mutter	Messing vernickelt
Unterlegling	FE vernickelt

Betriebstemperatur	-40/+70°C
Lagertemperatur	-40/+100°C

Material

Part	Material
Housing	Brass chromium plated
seal ring / sealing disk	NBR 70
Insulating part	Polycarbonate
Reflector	Polycarbonate transparent
Nut	Brass nickel plated
Washer	FE nickel plated

Operation Temperature	-40/+70°C
Storage Temperature	-40/+100°C

Optionen

Gehäuse mattchrom
Gehäuse glanzchrom

Options

Housing frosted chromium plated
Housing chromium plated

Artikel/ Part		Artikel-Text		Part-Text			
Spannung Voltage	Farbe Color	Lichtstärke Luminous intensity	Vollwinkel Viewing Angle	Lichtstrom luminous flux	Strom Current	Leistung Power	Lebensdauer live-time
SWDU14022 SigLeuØ14 ROT 12VAD IRsc							
12 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWDU14024 SigLeuØ14 ROT 24VAD IRsc							
24 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWDU14027 SigLeuØ14 ROT 130VA IRsc							
130 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWDU14028 SigLeuØ14 ROT 230VA IRsc							
230 V	 red rot	2.000 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWDU14122 SigLeuØ14 GELB 12VAD IRsc							
12 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWDU14124 SigLeuØ14 GELB 24VAD IRsc							
24 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWDU14127 SigLeuØ14 GELB 130VA IRsc							
130 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWDU14128 SigLeuØ14 GELB 230VA IRsc							
230 V	 yellow gelb	2.000 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWDU14422 SigLeuØ14 BLAU 12VAD IRsc							
12 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWDU14424 SigLeuØ14 BLAU 24VAD IRsc							
24 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWDU14427 SigLeuØ14 BLAU 130VAD IRsc							
130 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWDU14428 SigLeuØ14 BLAU 230VAD IRsc							
230 V	 blue blau	1.500 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWDU14622 SigLeuØ14 WEISS 12VAD IRsc							
12 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWDU14624 SigLeuØ14 WEISS 24AD IRsc							
24 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWDU14627 SigLeuØ14 WEISS 130VAD IRsc							
130 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h
SWDU14628 SigLeuØ14 WEISS 230VAD IRsc							
230 V	 white weiss	2.100 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h
SWDU14722 SigLeuØ14 UGRÜN 12VAD IRsc							
12 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	204 mW	50000 h
SWDU14724 SigLeuØ14 UGRÜN 24VAD IRsc							
24 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	408 mW	50000 h
SWDU14727 SigLeuØ14 UGRÜN 130VA IRsc							
130 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	2.210 mW	50000 h

Artikel/ Part		Artikel-Text		Part-Text			
Spannung Voltage	Farbe Color	Lichtstärke Luminous intensity	Vollwinkel Viewing Angle	Lichtstrom luminous flux	Strom Current	Leistung Power	Lebensdauer live-time
SWDU14728		SigLeuØ14 UGRÜN 230VA IRsc					
230 V	 ugreen ugrün	2.500 mcd/ 20,000 mA	30°	lm	17 mA	3.910 mW	50000 h

Layout FPI

Technische Änderungen vorbehalten. Datenblatt unterliegt nicht dem Änderungsdienst.
Die angegebenen technischen Daten sind typische Durchschnittswerte.

Wir achten bei der Entwicklung und Herstellung und beim Energieverbrauch unserer Produkte auf einen möglichst geringen Einsatz von Ressourcen.
Bitte prüfen Sie, ob es unbedingt erforderlich ist, das gesamte Dokument zu Drucken. So schonen Sie Ressourcen und unsere Umwelt.

Specifications are subject to change without notice.

The technical data are typical figures

*We care for environment when producing and manufacturing our products.
Also we care for a low power consumption and a low consumption of resources.
Please consider environmental responsibility before printing this e-mail*