




Notes

Electrical characteristics
Contact resistance: 20mΩ max. initial
Dielectrical withstanding voltage: 500V AC(rms) for 1 minute
Insulation resistance: 1000MΩ min.
Environment characteristics
Temperature range: -45°C to +105°C



Dimensions

Position	A ± 0.20	B ± 0.20	C ± 0.30	D
9	17.90	24.99	30.80	16.33
15	26.50	33.32	39.14	24.66
25	40.00	47.04	53.04	38.38
37	56.50	63.50	69.32	54.84

Tolerances

General tolerance		Angle tolerance	
x.	±0.60	x.	±5°
.x	±0.38	.x	±3°
.xx	±0.25	.xx	±2°