







NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BODY/CONTACT: BRASS PER JIS-C3604
2. INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL. 70 μ " THICK OVER COPPER STRIKE
6. GOLD PL. 1-3 μ " OVER NICKEL PL. 70 μ " THICK OVER COPPER STRIKE

4	Ferrule	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
No	Description	Material	Finish

Recommended Cable Stripping



- 1: CRIMPED CONTACT
HEX CRIMP SIZE: .068"
- 2: CRIMPED FERRULE
HEX CRIMP SIZE: .213"