

Electrical	
Impedance	50 Ω
Frequency range	0-4GHz
VSWR	≤ 1.2 typ
Test voltage	1500 volts rms
Working voltage	400 V rms
Voltage rating	500 volts peak
Power handling	≤ 80 W (2GHz)
Other (MIL-C-39012 Cable Connectors)	Contact resistance: center contact ≤ 1.5 mΩ outer contact ≤ 1 mΩ Insertion loss: ≤ 0.1α √f(GHz)dB Insulation resistance: ≥ 5000 mΩ
Material	
Mating cycles	≥ 500
Center contact captivation	Axial: ≥ 27 N
Environmental	
Temperature range	-65°C +165°C
Thermal shock	US MIL-STD 202, Meth. 107, Cond. B
Vibration	US MIL-STD 202, Meth. 204, Cond. B
Climatic class	IEC 60068 65/165/21
Shock	US MIL-STD 202, Meth. 213, Cond. B
Corrosion resistance	US MIL-STD 202, Meth. 101, Cond. B
Degree of protection (mated pair)	IEC 60529

6	Nut	Brass	Nickel
5	Ferrule	Brass	Nickel
4	Shell	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
NO	Description	Material	Finish

