

Features

Switching Regulator

- Efficiency up to 96%, no need for heatsinks
- 4.5 - 36VDC wide input voltage
- -40°C to +90°C ambient operation without derating
- Pin compatible with 78 series regulators
- Non isolated DC/DC converter
- Undervoltage and short circuit protection

RECOM
DC/DC Converter

R-78K-2.0

2.0 Amp
SIP3
Single Output



IEC/EN62368-1 3rd Edition certified
EN55032 compliant
CB-Report

Description

The R-78K-2.0 series is a switching regulator module that has been designed to offer all the advantages of a switching regulator (high efficiency, wide input range, accurate output voltage regulation) but with a low cost for production quantities. Due to the R-78K-2.0's high efficiency of up to 96% no heat-sink is required, and operation from -40 to 90°C is possible without derating. The compact TO-220 compatible SIP3 package measures only 11.5 x 8.5 x 17.5, so it saves precious board space.

Selection Guide

Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Current [mA]	Efficiency @ min. Vin [%]	Efficiency @ max. Vin [%]
R-78K1.2-2.0	4.5 - 36	1.2	2000	75	73
R-78K1.5-2.0	4.5 - 36	1.5	2000	82	71
R-78K1.8-2.0	4.5 - 36	1.8	2000	85	78
R-78K2.5-2.0	4.5 - 36	2.5	2000	88	85
R-78K3.3-2.0	4.5 - 36	3.3	2000	85	78
R-78K5.0-2.0	6.5 - 36	5	2000	85	78
R-78K9.0-2.0	11 - 36	9	2000	95	93
R-78K12-2.0	14 - 36	12	2000	96	94
R-78K15-2.0	18 - 36	15	2000	96	94

Model Numbering

R-78K **-2.0**
nom. Output Voltage Output Current

Specifications

ABSOLUTE MAX RATINGS (exceeding these ratings may damage the device)

Parameter	Condition	Min.	Typ.	Max.
Maximum Input Voltage Slew Rate ⁽²⁾	+V _{IN} to GND			10VDC/μs
Case Temperature		-40°C		110°C
Storage Temperature		-50°C		125°C

Notes:

Note2: At higher slew rates or hard plugging, add 27μF E-Cap between +Vin and GND, especially when Vin is >18VDC

Specifications (measured @ $T_a = -40^{\circ}\text{C}$ to $+90^{\circ}\text{C}$, $V_{IN} = 24\text{VDC}$, full load and after warm-up unless otherwise stated)

BASIC CHARACTERISTICS


Parameter	Condition	Min.	Typ.	Max.
Input Under Voltage Lockout (UVLO)	R-78K1.2-2.0, R-78K1.5-2.0, R-78K1.8-2.0, R-78K2.5-2.0, R-78K3.3-2.0	DC-DC ON	4VDC	4.4VDC
		DC-DC OFF	3.8VDC	4.2VDC
	R-78K5.0-2.0	DC-DC ON	5VDC	6.5VDC
		DC-DC OFF	4.8VDC	6.3VDC
	R-78K9.0-2.0	DC-DC ON	9.9VDC	10.7VDC
		DC-DC OFF	9.7VDC	10.5VDC
	R-78K12-2.0	DC-DC ON	13.1VDC	14.0VDC
		DC-DC OFF	12.7VDC	13.8VDC
	R-78K15-2.0	DC-DC ON	15.4VDC	16.7VDC
		DC-DC OFF	15.2VDC	16.5VDC
Quiescent Current				1mA
Internal Switching Frequency			400kHz	
Minimum Load		0%		
Output Ripple and Noise ⁽³⁾	20MHz BW	others	100mVp-p	120mVp-p
		R-78K12-2.0	170mVp-p	200mVp-p
		R-78K15-2.0	200mVp-p	250mVp-p

Notes:


Note3: Measurements are made with a 0.1 μF MLCC & 10 μF E-cap across output (low ESR)

R-78K1.2-2.0

Efficiency vs. Load



Power Dissipation vs. Load




continued on next page


Specifications (measured @ $T_a = -40^{\circ}\text{C}$ to $+90^{\circ}\text{C}$, $V_{IN} = 24\text{VDC}$, full load and after warm-up unless otherwise stated)

R-78K1.5-2.0

Efficiency vs. Load




Power Dissipation vs. Load




R-78K1.8-2.0

Efficiency vs. Load




Power Dissipation vs. Load




R-78K2.5-2.0

Efficiency vs. Load



Power Dissipation vs. Load




continued on next page


Specifications (measured @ $T_a = -40^\circ\text{C}$ to $+90^\circ\text{C}$, $V_{IN} = 24\text{VDC}$, full load and after warm-up unless otherwise stated)

R-78K3.3-2.0

Efficiency vs. Load




Power Dissipation vs. Load




R-78K5.0-2.0

Efficiency vs. Load




Power Dissipation vs. Load




R-78K9.0-2.0

Efficiency vs. Load




Power Dissipation vs. Load




Specifications (measured @ $T_a = -40^{\circ}\text{C}$ to $+90^{\circ}\text{C}$, $V_{IN} = 24\text{VDC}$, full load and after warm-up unless otherwise stated)

R-78K12-2.0

Efficiency vs. Load




Power Dissipation vs. Load




R-78K15-2.0

Efficiency vs. Load



Power Dissipation vs. Load



REGULATIONS

Parameter	Condition	Value
Output Accuracy		$\pm 3.0\%$ typ.
Line Regulation	low line to high line, full load	$\pm 0.5\%$ max.
Load Regulation	0% to 100%	4.0% max.

Specifications (measured @ $T_a = -40^\circ\text{C}$ to $+90^\circ\text{C}$, $V_{in} = 24\text{VDC}$, full load and after warm-up unless otherwise stated)

PROTECTIONS


Parameter	Condition	Value
Short Circuit Protection (SCP)		continuous, automatic recovery
Short Circuit Input Current		50mA max.

Optional Diode Protection Circuit


Add a blocking diode to V_{out} if current can flow backwards into the output, as this can damage the converter when it is powered down.

The diode can either be fitted across the device if the source is low impedance or fitted in series with the output (recommended).

Optional Protection 1:



Optional Protection 2:





ENVIRONMENTAL

Parameter	Condition	Value
Operating Temperature Range	with derating, refer to "Derating Graph"	-40°C to $+90^\circ\text{C}$
Maximum Case Temperature		$+110^\circ\text{C}$
Temperature Coefficient		0.01%/K
Operating Humidity	non-condensing	95% RH max.
MTBF	according to MIL-HDBK-217F, G.B., $+25^\circ\text{C}$	R-78K1.8-2.0
		R-78K2.5-2.0
		R-78K3.3-2.0
		R-78K5.0-2.0
		R-78K9.0-2.0
		R-78K12-2.0
		R-78K15-2.0
Vibration		10-55Hz, 2G, 30min along X,Y and Z axis


Derating Graph

(@ Chamber and natural convection 0.1m/s)



continued on next page

Specifications (measured @ $T_a = -40^{\circ}\text{C}$ to $+90^{\circ}\text{C}$, $V_{IN} = 24\text{VDC}$, full load and after warm-up unless otherwise stated)




SAFETY AND CERTIFICATIONS (PENDING)

Certificate Type (Safety)	Report Number	Standard
Audio/Video, information and communication technology equipment - Part 1: Safety requirements 3rd Edition (CB Scheme)	085-220299301-100	IEC62368-1:2018 3rd Edition
Audio/Video, information and communication technology equipment - Part 1: Safety requirements 3rd Edition		EN IEC 62368-1:2020+A11:2020
RoHS2		RoHS 2011/65/EU + AM2015/863

EMC Compliance

Condition	Standard / Criterion
Electromagnetic compatibility of multimedia equipment - Emission requirements	with external filter EN55032, Class B

EMC filtering suggestions according to EN55032



Component List Class B



Vin Range	CE1	C1/C2	L1	C3	L2	C4
4.5 - 36	100μF	10μF	22μH	N/A	N/A	1nF
11 - 36	N/A	10μF	22μH	1nF	4.7μH	1nF

Specifications (measured @ $T_a = -40^{\circ}\text{C}$ to $+90^{\circ}\text{C}$, $V_{IN} = 24\text{VDC}$, full load and after warm-up unless otherwise stated)

DIMENSION AND PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	case	black plastic, (UL94 V-0)
	potting	PU, (UL94 V-0)
	PCB	FR4, (UL94 V-0)
Dimension (LxWxH)		11.5 x 8.5 x 17.5mm
Weight		4g typ.

Dimension Drawing (mm)



Pinning Information

Pin #	Single
1	+V _{IN}
2	GND
3	+V _{OUT}

Tolerance:
xx.x = ±0.5mm
xx.xx = ±0.25mm

PACKAGING INFORMATION

Parameter	Type	Value
Packaging Dimension (LxWxH)	tube	520.0 x 25.5 x 10.5mm
Packaging Quantity		43pcs
Storage Temperature Range		-50°C to +125°C
Storage Humidity	non-condensing	95% RH max.

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.