

GP Batteries

Data Sheet


Model No.: GP13G

NO MERCURY ADDED

Description : Mercury Free Extra Heavy Duty Battery, D Size
 Chemical System : Zinc Chloride
 Nominal Voltage : 1.5 Volts
 Nominal Dimensions : $\varnothing 34.2$ mm x 61.5 mm
 Terminals : Protruded positive(+) and flat negative(-) contacts
 Jacket : Metal jacket with PVC tube insulation
 Applications : All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, portables fans, portables hand-tools.
 Shelf Life : 24 months
 Average Weight : 102g
 Date Code : Unless otherwise specified, every battery will carry an expiry date code for 24 months. (e.g. a battery manufactured on January 2000 will carry an expiry code of 01-02.) 01 stands for January, 02 stands for 2002

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
39 Ohms	4 Hrs/ Day	0.9V	200 Hrs
3.9 Ohms	1 Hr/ Day	1.0V	12.1 Hrs



Cross References:

GP	JIS	IEC	Eveready
13G	R20P	R20	1250

