



**Material :**

- contacts Au/Ni
- flexible insulator
- wire = silicone  
7 x 0,20 = 0,22 mm<sup>2</sup>
- outer Ø = 1,4 mm


**Matière :**

- contacts Au/Ni
- isolant souple
- câble = silicone  
7 x 0,20 = 0,22 mm<sup>2</sup>
- Ø extérieur = 1,4 mm


**Material :**

- Kontakte Au/Ni
- Isolation
- Litze = Silikon  
7 x 0,20 = 0,22 mm<sup>2</sup>
- Äusserer Ø 1,4 mm


**Type 1**




**Type 2**



**Type 3**




**Type 4**




**Type 5**




**Type 6**





**Type 7**



**Type 8**



Examples of other combinations  
Exemples d'autres combinaisons  
Beispiele von anderen Kombinationen



Type	Reference Référence Bestell-Nr	L cm	Max current I admissible Bemessungs- strom	Max voltage Tension maxi Bemessungs- spannung	m Ω max	Pack	Colours Couleurs Farben #
1	209050-F-F-10 #	10	2A	< 33 V. AC  < 70 V. DC	8	10	R
	209050-F-F-20 #	20			12		N
2	209050-M-F-10 #	10			8		Bl
	209050-M-F-20 #	20			12		V
3	209050-M-M-10 #	10			8		Gr
	209050-M-M-20 #	20			12		J
4	209078-F-F-10 #	10			8		Ye
	209078-F-F-20 #	20			12		Wh
5	209078-M-F-10 #	10	8				
	209078-M-F-20 #	20	12				
6	209078-M-M-10 #	10	8				
	209078-M-M-20 #	20	12				
7	209080-AR-10 #	10	8				
	209080-AR-20 #	20	12				
8	209100-AR-10 #	10	8				
	209100-AR-20 #	20	12				

and so on ... consult us  
etc. ... nous consulter  
usw ... Auf Anfrage