




POSITION	A	B	C
10	10.16	32.00	21.84
14	15.24	37.08	26.92
16	17.78	39.62	29.46
20	22.86	44.70	34.54
24	27.94	49.78	39.62
26	30.48	52.32	42.16
30	35.56	57.40	47.24
34	40.64	62.48	52.32
40	48.26	70.10	59.94
50	60.96	82.80	72.64
60	73.66	95.50	85.34
64	78.74	100.58	90.42



RoHS COMPLIANT

TITLE: 2.54MM SHROUDED HEADER STRAIGHT PCB
MOUNT TYPE WITH SHORT EJECTORS

Recommended PCB Layout



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL94V-0

Insulator Color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate on mating area, Tin over Copper underplate on solder tail

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -55° to +105°



Distributed by Conrad Electronic SE • Klaus-Conrad-Str. 1 • D-92240 Hirschau

Datasheet

Item no. 001581009

V1_0617_02