

## Product data sheet Qomo QWB100WS-PS

# Qomo QWB100WS-PS

This model is our biggest Interactive Infrared Whiteboard. It measures has a 96 inch writeable surface.

Qomo Interactive Whiteboards are changing the way many educators engage students and present their material. Perfect for the classroom or any where there is a need for interactive instruction. Teachers are free to use the supplied felt Pens, extension Wand or even their fingers to annotate over any application on the computer screen. Using advanced Infrared (IR) technology, the Qomo interactive whiteboard recognizes the touch of your pen, or your finger, and can track them anywhere on the screen. The porcelain steel erasable surface of the Qomo board is durable and allows you to use the interactive whiteboard as a dry erase board. Thanks to this feature the surface produces virtually no glare and is very easy to keep clean. At the bottom of the screen this model houses a onboard pen tray to hold the 3 pens, extension wand and eraser. The versatile board is typically mounted to a wall or floor stand and easily integrates into a complete conference network. Qomo's flexible and easy to use Flow! Works annotation software is included with every Qomo whiteboard.



## Features

- **Erasable porcelain surface**
- **Using advanced IR technology it recognizes the pen or finger and can track you anywhere on the screen**
- **Easily integrates into a complete conference network**
- **Surface is durable, cleans up easily and is coated to provide minimal glare**
- **Flow! Works annotation software included**
- **Annotate over any application and save your work**

**Product data sheet Qomo QWB100WS-PS**

<b>Model</b>	<b>Qomo QWB100WS-PS H01</b>
Active Area	96"
Projection Size	201x 114 cm
Sensitive Area Size	215 x 116 cm
Outside Dimensions	232 x 130 x 4 cm
Technology	Infra-Red
Frame	Brusched Aluminium
Surface	Anti-Glare/ Porcelain Steel
Dry Erasable	Yes
Screen ratio	16:9
Write Method	Pen, Wand or Finger
Multitouch	Yes (4x)
Pen tray	Yes
Active Tray	Yes
Hotkeys	Yes
Resolution	4096x4096
Response speed 1st Touch	25Ms
Response speed Continuous touch	8 Ms
Cursor Speed	3,048 mm/s
Location Accuracy	3 mm
Power consumption	<0,4W
Connection	USB
OS	Windows 2000 / XP / Vista / 7 / 8 / Mac / Linux*
Working Temp	-15C/+50C
Humidity	20%~95%
Storage temperature	-40C/ +50C
Weight	30 Kg

## Product data sheet Qomo QWB100WS-PS

### Content Box

CD-Rom	Yes
--------	-----

USB Cable	Yes
-----------	-----

3 Interactive pens	Yes
--------------------	-----

Wand	Yes
------	-----

Eraser	Yes
--------	-----

Wall Mount Kit	Yes
----------------	-----

### Dimensions

Packing Size	252 x 141 x 9 cm
--------------	------------------

Gross Weight	40 Kg
--------------	-------

Storage temp	-40C/ +50C
--------------	------------

### Optional

Mobile Floor Stand	Yes
--------------------	-----

RF Wireless Kit	Yes
-----------------	-----

\* Mac and Linux Support for select OS versions

