


Product data sheet Qomo QIT1065 LED screen

Qomo QIT1065 65” Multi-Touch Screen

The QIT1065 LED Multi-Touch Screen is an easy to use, sleek, interactive presentation solution that displays a cristal clear image and has virtually no delay when annotating.

This LED screen is great for use in a classroom, conference room or showroom, or anywhere where an easy-to-use interactive presentation solution is needed. The 65 inch 1080p HD LED screen with toughened glass requires no projector, which eliminates projector installations, expensive projector bulbs and a projection shadow. Simply turn on the screen and you are ready to present. Presenters can use our annotation software, Flow!Works, to create lessons, or annotate over pre-made PowerPoints or any online resources.

- **Requires no projector, simply turn on and start**
- **65 inch active screen size**
- **5.5ms response time (No lag – fast response)**
- **1080p HD resolution**
- **6 touch points**



Product data sheet Qomo QIT1065 LED screen

Screen	QIT 1065
Screen Type	TFT LCD with LED
Display Area	143x 80 cm
Dimensions	155x92x10 cm
Weight	67 Kg
Mounting	Wall or Stand
Display Ratio	16:9
Resolution	1920x 1080
Display Colors	10Bit/ 1.07B
Brightness	280-360 cd/m2
Contrast Ratio	4000:1
Response time	5,5ms
Refreshing Frequency	120Hz
View Angle (H/V)	178/178
Storage of channels	125
Videosystems	PAL-D/K/I

AV Inputs

USB Media Play	1
USB Touch Frame	3
HDMI	2
S-Video	1
YPbPr/YCbCr/Audio	2
PC Audio	3
AV	1
RS232	1

Product data sheet Qomo QIT1065 LED screen**AV Outputs**

SPDIF	1
VGA	1
Speaker output	2x10W
Multimedia Support	
Image	JPEG, BMP, PNG
Video	MPEG1,2 and 4, H264, RM, RMVB, MOV, MJPEG, VC1, Divx, FLV (support 1080P HD Decoding)
Audio	WMA, MP3, M4A (AAC)

Power consumption

Maximum	<220W
Energy Saving Mode	<150W
Stand By	<1W
Voltage	AC 100-240, 50/60Hz

Touch screen

Surface	Toughened Glass
Anti-Glare	Y
Touch Sensor	IR
USB Type	HID
Touch Points	6
Writing Tools	Pen or finger
Touch resolution	4096x4096
Scan Speed	8ms
Cursor Speed	120 Points/s
Positioning Accuracy	1mm

