Edge Series Microscope Eyepiece Digital Camera

AM7025X

Product Overview

The first eyepiece with the high quality Edge Series class optics and high-resolution sensor, the 5MP Dino-Eye Edge Series AM7025X offers remarkable image performance while providing a relatively larger field of view than its predecessors.

The AM7025X design and included adapters allows for fitment within 23mm, 30mm, 30.5mm or c-mount eyepiece slots which can be fixed into ideal focal positions. With fine color reproducibility, the AM7025X is capable of capturing the finest details of a microscope's view for a wide range of professional applications



Details

Base Magnification	20x
Sensor Type	CMOS
Resolution	2592 × 1944 pixels
Megapixels	5 MP
Frame Rate (max)	30 FPS
Operating System	Windows XP, Vista, 7, 8, 10, Mac OS 10.9 (Mavericks), Mac OS 10.10 (Yosemite)
Included Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Connection Type	USB 2.0
Image Save Formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Image Save Formats (Mac OS)	JPEG, PNG
Video Save Formats (Windows)	WMV, FLV, SWF
Video Save Formats (Mac OS)	MOV



Base Diameter	23mm
Dimensions	8.0cm (H) x 3.2cm (D)
Weight	117g (7025X)
Cable Length	182cm (71.65 in)
Body Material	Metal
Measurement	Yes
Package Includes	Camera, Edge Calibration Target
Warranty Period	2 years
Manufactured in	Taiwan
Service & Support	U.S. (www.dinolite.us) English & Spanish
Regulatory Approval	CE, FCC

Web page: https://dinolite.us/products/am7025x

Dino-Lite US / Dunwell Tech, Inc https://www.dinolite.us Toll free: 888-668-2442 Phone: +1 310 618 9990 sales@dunwell.com

