

## **USB to DVI Adapter - External USB Video Graphics Card for PC and MAC- 1920x1200**

*StarTech ID: USB2DVIPRO2*



The USB2DVIPRO2 USB to DVI Adapter functions as an external graphics card for Windows® and Mac® computers - the perfect solution for turning your desktop or laptop computer into a dual or multi-monitor environment, all through the simplicity and convenience of USB.

The USB-DVI Adapter delivers high quality video (up to 1920x1200) for a variety of applications and is capable of simultaneously running up to five additional displays from a single computer (using four USB2DVIPRO2 External Video Adapters). The adapter connects to a host computer through a USB 2.0 port, acting as an external DVI video card to either extend or mirror the desktop shown on the existing display - without having to open the computer case.

Featuring driver support for Microsoft Windows® (including Aero themes) and Mac OS X, and with video support for resolutions up to 1920x1200, this USB-DVI video adapter is the ideal solution for a wide range of operating environments as well as large-screen displays/monitors.

The USB2DVIPRO2 USB to DVI Adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.



## Applications

- Add multiple (up to five) monitors / projectors to your computer setup using one USB2DVIPRO2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- Increase productivity by running multiple applications on different DVI screens; check your email on one display while editing a document on the other
- Use the USB-DVI adapter to connect your PC to your television for showing family pictures and movies
- Connect multiple DVI monitors to a single computer to create engaging multimedia presentations
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

## Features

- Support for Aero themes in Windows®
- Works with Mac® OS X
- Optimal performance at 1920x1200 and ideal for use with 24" to 26" monitors or smaller
- USB-Powered operation, no external power adapter required
- Quick and easy installation
- Powered by DisplayLink DL-195 chip



## Technical Specifications

Warranty	2 Years
Chipset ID	DisplayLink - DL-195
Memory	16MB
Output Signal	DVI-I (DVI Digital/Analog)
USB Pass-Through	No
General Specifications	This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a Trigger or Fresco family chipset.
Maximum Digital Resolutions	1920x1200 (32-bit color)
MTBF	621,445 Hours
Supported Resolutions	Widescreen (16/32 bit): 1920x1200, 1680x1050, 1440x900, 1366x768  Standard (16/32 bit): 1600x1200, 1280x1024, 1024x768, 800x600, 640x480
Connector Type(s)	1 - DVI-I (29 pin) Female
Connector Type(s)	1 - USB A (4 pin) Male
OS Compatibility	Windows® 10 (32/64), 8/8.1 (32/64), 7 (32/64), Vista (32/64), XP (32/64), 2000 (Aero 3D interface supported) Apple® OSX El Capitan (10.11), Yosemite (10.10), Mavericks (10.9) Mountain Lion (10.8), Lion (10.7), Snow Leopard (10.6) Chrome® OS v51
<b>Note</b>	Power PC-based Macintosh computers, such as late-model iMacs, PowerBooks and PowerMacs, are not currently supported
System and Cable Requirements	1.2Ghz or higher CPU 30MB of hard drive space 512 MB RAM USB 2.0 Port
LED Indicators	1 - Blue - Power
Power Source	USB-Powered



Humidity	<85% non-condensing
Operating Temperature	10°C to 40°C (50°F to 104°F)
Storage Temperature	-10°C to 80°C (14°F to 176°F)
Color	Black
Product Height	0.8 in [20 mm]
Product Length	10.6 in [270 mm]
Product Weight	2.5 oz [72 g]
Product Width	2.2 in [55 mm]
Shipping (Package) Weight	9 oz [254 g]
Included in Package	1 - USB to DVI Adapter
Included in Package	1 - DVI to VGA adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual



Certifications, Reports and Compatibility

