

## **Slim USB 3.0 to VGA External Video Card Multi Monitor Adapter – 1920x1200 / 1080p**

*StarTech ID: USB32VGAES*



The USB32VGAES Slim USB 3.0 to VGA Adapter turns a USB 3.0 port into a VGA output port with 1920x1200/1080p video support. The adapter minimizes clutter with a slim design that seamlessly blends with your video cable - an ideal space-saving solution for multi-monitor applications on Ultrabook™, laptop, or desktop computers.

Functioning as an external graphics card, this USB to VGA adapter provides a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0).

To save space while travelling, this ultra-portable USB to VGA adapter features a lightweight, small footprint design that fits easily in a laptop carrying bag.

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter delivers smooth, high-definition content to your VGA display/projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

The USB32VGAES is backed by a StarTech.com 2-year warranty and free lifetime technical support.





**Recommended System Requirements:**

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

USB 3.0 port (Backwards compatible with USB 2.0)

**Applications**

- Add a secondary VGA display with full HD capability
- View large or multiple spreadsheets across several displays
- Use the adapter to connect your PC to your VGA-equipped projector or display for viewing family pictures and movies
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Have reference material on one display and a working document copy on the other
- Run multiple applications on different screens - check your email on one display and search the web on the other

**Features**

- Slim lightweight design
- Ultra-portable
- SuperSpeed USB 3.0 (5 Gbps)
- Supports High-Definition video resolutions up to 1920x1200/1080p
- USB-powered - No external power adapter required
- Supports Mirrored, Extended or Primary display configurations
- Supports display rotation

## Technical Specifications

Warranty	2 Years
Chipset ID	T5-302/MCT
Ports	1
USB Pass-Through	No
General Specifications	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.
Maximum Analog Resolutions	1920x1200/1080p
Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720  Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
Wide Screen Supported	Yes
Connector A	1 - USB 3.0 A (9 pin; SuperSpeed) Male Input
Connector B	1 - VGA (15 pin; High Density D-Sub) Female Output
Microsoft WHQL Certified	Yes
OS Compatibility	Windows® 10 (32/64) Windows 8 / 8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64)
<b>Note</b>	Connect a maximum of five USB32VGAES adapters on a single PC - See manual for system requirements
System and Cable Requirements	CPU: i3 Dual core 2.8GHz RAM: 2GB or higher  Full HD Video: CPU: Quad Core 2.4GHz or Higher (i5 recommended) RAM: 4GB or higher

Power Source	USB-Powered
Humidity	< 85% non-condensing
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-10°C to 75°C (14°F to 167°F)
Cable Length	2.4 in [62 mm]
Color	Black
Enclosure Type	Plastic
Product Height	0.5 in [12 mm]
Product Length	7.5 in [190 mm]
Product Weight	0.9 oz [25 g]
Product Width	1 in [25 mm]
Shipping (Package) Weight	0 lb [0 kg]
Included in Package	1 - Slim USB 3.0 Video Adapter
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

