









Data Sheet



(t=2.0MAX)

REVISION			
LTR	DESCRIPTION	DATE	APRO
△	Changed Material (BSBM to STEEL)	06/08/21	M.K
△	Changed Width (11mm to 10mm) 11mm→10mm	06/08/21	M.K
△	Changed Pitch (1.0 to 0.75) P1.0→P0.75	06/08/21	M.K

SPECIFICATION

DIELECTRIC STRENGTH:500V AC FOR ONE MINUTE.
CONTACT RESISTANCE:50mΩ MAX
INSULATION RESISTANCE:100MΩ MIN.AT 500V DC.

						TOLERANCE	SCALE	DATE	DESIG	DRAW	INSPE	APRO
							2/1	02/10/24	K.S	N.1		M.K
6	HEX NUT	STEEL △	1	Ni		MODEL		QTY	PART NAME	3-con. 2.5mm Panel Mtg..Jack No.MJ-071H		
5	CONTACT C	BSR t=0.3	1	Ni		MATERIAL			DRAW.NO	MJ071H		
4	CONTACT B	FAB-EH t=0.25	1	Ni		FINISH						
3	CONTACT A	FAB-EH t=0.25	1	Au								
2	SLEEVE	BSBM	1	Au								
1	HOUSING	PA	1									
LET	PARTNAME	MATERIAL	QTY	FINISH	NOTE							