

7.62mm Female Pluggable Horizontal 15A Terminal Blocks

Specifications

Pitch:	7.62mm
Type:	90°, Pluggable
Poles:	2 to 12
Rated Voltage:	See Table
Rated Current:	See Table
Operational Temperature:	-40°C to +105°C
Withstand Voltage:	2500V AC for 60s
Insulation Resistance:	500MΩ at 500V DC
Wire Range:	See Table
Wire Stripping Length:	6-7mm ± 0.5mm
Screw Size:	M2.5
Max. Torque Value:	0.4Nm
Wave Soldering:	260°C for 5s
Hand Soldering:	350°C for 10s





Colour and Materials

Housing Colour:	Green
Housing Material:	PA66
Flame Retardancy:	UL94-V0
Screw:	Zinc-plated steel (A3)
Wire Cage:	Nickel-plated brass
Contact:	Phosphor bronze



Order Code	Poles	Order Code	Poles
21-1889	2	21-1894	8
21-1890	3	21-1995	9
21-1891	4	21-1895	10
21-1892	5	21-1996	11
21-1893	6	21-1896	12
21-1994	7		

Standard	Rated Voltage	Rated Current	Wire Range
UL	300V	15A	28-12AWG (0.08-4mm ²)
IEC	400V	20A	2.5mm ²



Measurements are in mm
unless stated otherwise.

