


Order code	Manufacturer code	Description
23-0104	n/a	16A HIGH CURRENT APPLIANCE INLET (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003



**High current appliance inlet
Type 4798**

Screw-on mounting from front
Solder or quick-connect terminals
Pin temperature 70 °C
Protection class I




**Gerätestecker für höhere Ströme
Typ 4798**

Schraubmontage von vorn
Löt- oder Steckanschlüsse
Stifttemperatur 70 °C
Schutzklasse I




**High current appliance inlet
Type 4793**

Snap-in mounting from front
Solder or quick-connect terminals
Pin temperature 70 °C
Protection class I



**Gerätestecker für höhere Ströme
Typ 4793**

Schnappmontage von vorn
Löt- oder Steckanschlüsse
Stifttemperatur 70 °C
Schutzklasse I



Details Types / Typen 4798, 4793

Technical data

- Rated current/voltage: 16 A/250 VAC
- Insulation resistance: > 10 MΩ (500 VDC, 1 Min.)
- Dielectric strength: 2 kV (50 Hz, 1 Min.), to accessible surfaces
- Material: Socket: Thermoplastic UL 94 V-0 black

Technische Daten

- Nennstrom/-spannung: 16 A/250 VAC
- Isolationswiderstand: > 10 MΩ (500 VDC, 1 Min.)
- Spannungsfestigkeit: 2 kV (50 Hz, 1 Min.), zu berührbaren Oberflächen
- Material: Socket: Thermoplast UL 94 V-0 schwarz

Standards / Normen

IEC/EN 60320-1/C20
UL 498, CSA 22,2

Approvals / Approbationen: Inlet Type 4798

- VDE (16 A / 250 VAC)
- UL (20 A / 250 VAC)
- CSA (22 A / 250 VAC)

Approvals / Approbationen: Inlet Type 4793

- VDE (16 A / 250 VAC)
- UL/CSA (20 A / 250 VAC)

Order Numbers / Bestell-Nummern

Screw-on mounting/ Schraubmontage Type / Typ 4798	Snap-in mounting / Schnappmontage Type / Typ 4793						Terminals / Anschlüsse
	Panel thickness s / Plattendicke s						
	1,0 mm	1,2 mm	1,5 mm	2,0 mm	2,5 mm	3,0 mm	
4798.9000	4793.3000	4793.8000	4793.4000	4793.5000	4793.6000	4793.7000	Quick-connect terminals 6,3 x 0,8 mm / Steckanschlüsse 6,3 x 0,8 mm
4798.9200	4793.3200	4793.8200	4793.4200	4793.5200	4793.6200	4793.7200	Solder terminals / Lötanschlüsse