


Order code	Manufacturer code	Description
23-3221	n/a	SCREW ON POWER ENTRY MODULE RED
23-3223	n/a	SCREW ON POWER ENTRY MODULE GREEN

	Page 1 of 3
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003

Actual information about approvals can be found on
<http://www.schurter.com/approvals>



C14



70 °C

Description

- Panel mount:
Screw-on version from front or rear side, snap-in version from front side
- 2 Functions:
Connector Protection class I, Line switch 2-pole
- Quick connect terminals 4.8 x 0.8 mm
- Alternative: version with line filter [KFB2](#)
- We recommend for new applications type [DC11](#)

Characteristics

- All single elements are already wired
Unwired versions available on request
- Line switch non-illuminated or illuminated

Other versions on request:

- unwired versions
- line switch with other rocker marking
- for protection class II


Technical data

Ratings IEC	10 A / 250 VAC; 50 Hz
Ratings UL/CSA	15 A / 250 VAC; 60 Hz
Dielectric strength	> 2.5 kVAC between L-N > 3 kVAC between L/N-PE (1 min/50 Hz)
Allowable operation temp.	-25 °C to 70 °C
Degree of protection	from front side IP40 acc. to IEC 60529
Protection class	Suitable for appliances with protection class I acc. to IEC 61140
Terminals	Quick connect terminals 4.8 x 0.8 mm
Panel thickness s	Screw-on: max 6 mm Mounting screw torque max 0.5 Nm Snap-in: 1.5/2/2.5 mm
Materials: Housing	Thermoplastic, black, UL 94V-0


Appliance-inlet /-outlet	C14 acc. to IEC/EN 60320-1, UL 498, CSA C22.2 no. 42 (for cold condition) pin-temperature 70 °C, 10 A, Protection class I
Line switch	Rocker switch 2-pole, non-illuminated or illuminated red or green, acc. to IEC 61058-1 Technical details GENERAL PRODUCT INFORMATION

Dimensions


Screw-on mounting



Snap-in mounting



Diagrams



Variants

with internal connections

Order Number	Panel mounting	Panel thickness s [mm]	Illumination	Rated voltage 125/250 [V]	Color
4302.2102	Snap-in	1.5	●	250	red
4302.2103	Snap-in	2	●	250	red
4302.2104	Snap-in	2.5	●	250	red
4302.2142	Snap-in	1.5	●	250	green
4302.2143	Snap-in	2	●	250	green
4302.2144	Snap-in	2.5	●	250	green
4302.2002	Snap-in	1.5			
4302.2003	Snap-in	2			
4302.2004	Snap-in	2.5			
4302.2101	Screw-on		●	250	red
4302.2141	Screw-on		●	250	green
4302.2001	Screw-on				