


Order code	Manufacturer code	Description
23-3453	n/a	SCREW-ON MOUNT APPLIANCE OUTLET (RC)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change 'without notice' due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 04/07/2003


**Backplane Outlet  
Type 4787**

Screw-on mounting from front  
Solder- or quick-connect terminals  
Pin temperature 70 °C  
Protection class I




**Gerätesteckdose für  
Rückwand-Montage  
Typ 4787**

Schraubmontage von vorn  
Löt- oder Steckanschlüsse  
Stifttemperatur 70 °C  
Schutzklasse I





**Backplane Outlet  
Type 4788**

Snap-in mounting from front  
Solder- or quick-connect terminals  
Pin temperature 70 °C  
Protection class I



**Gerätesteckdose für  
Rückwand-Montage  
Typ 4788**

Snap-in-Montage von vorn  
Löt- oder Steckanschlüsse  
Stifttemperatur 70 °C  
Schutzklasse I



**Details Types / Typen 4787, 4788**

**Technical data**

- Rated current/voltage: 10 A/250 VAC
- Insulation resistance: > 10 MΩ (500 VDC, 1 Min.)
- Dielectric strength: 2 kV (50 Hz, 1 Min.), to accessible surfaces
- Material:
  - Body thermoplastic, black, UL 94 V-0

**Technische Daten**

- Nennstrom/-spannung: 10 A/250 VAC
- Isolationswiderstand: > 10 MΩ (500 VDC, 1 Min.)
- Spannungsfestigkeit: 2 kV (50 Hz, 1 Min.), zu berührbaren Oberflächen
- Material:
  - Gehäuse aus Thermoplast, schwarz, UL 94 V-0

**Standards / Normen**

IEC/EN 60320-2-2/F

**Approvals / Approbationen**

- VDE (10 A / 250 VAC); Typen 4787, 4788
- CSA (15 A / 250 VAC); Type 4787
- UL (15 A / 250 VAC); Type 4787
- c us UL (15 A / 250 VAC); Type 4788

**Order Numbers / Bestell-Nummern**

Screw-on mounting / Schraubmontage	Snap-in mounting / Snap-in-Montage						Terminals / Anschlüsse
	Panel thickness s / Plattendicke s						
	1,0 mm	1,2 mm	1,5 mm	2,0 mm	2,5 mm	3,0 mm	
4787.1000	4788.3000	4788.8000	4788.4000	4788.5000	4788.6000	4788.7000	Quick-connect terminals 6,3 x 0,8 mm / Steckanschlüsse 6,3 x 0,8 mm
4787.2000	4788.3100	4788.8100	4788.4100	4788.5100	4788.6100	4788.7100	Solder-/quick-connect terminals 4,8 x 0,8 mm Löt-/Steckanschlüsse 4,8 x 0,8 mm