

DATA SHEET

2.54mm PCB connectors

Order code	Manufacturer code	Description
22-2576	n/a	REEL 1000 0.156" CRIMP TERMINAL (RC)


2.54mm PCB connectors	Page 1 of 2
The enclosed information is believed to be correct, Information may change ±without noticeqdue to	Revision A
product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	20/02/2007

Sales: 01206 751166 Sales@rapidelec.co.uk Technical: 01206 835555 Tech@rapidelec.co.uk Fax: 01206 751188 www.rapidonline.com

22-2576

EVER-CONN E.C.I.

8578 SERIES



THICKNESS: D.25mm & 0.30mm
MATT: BRASS ER PHISPHER BRONZE TIN PLATED

CURRENT RATING 50-7A AC,DC VOLTAGE RATING 250V AC,DC APPLICABLE WIRE RANGE AVE#16-20

TUV FILE NO: 93 02 14023 512

MATES WITH: 8639, 8669, 3095-05, 5080 & 7500 SERIES HOUSENG

ACCEPTS WITH 114 MM (1045") SQUARE PIN

UL FILE NO. EMS256 CSA FILE NO. LR84767

TOTAL S REV 0 ±0.4 ±0.5 MARK ETISE 4. and will 20-4040 UP LAY 12003 153 ER DIG NO. DATE ±0.2 ±0.3 TYPE 90.18, 25 8578 1-10 10-20 PARTIT