





Datasheet

Item no. 1586514

V1_0617_02_EN



RECOMMENDED P.C.B LAYOUT
(TOLERANCE: ±0.05)

NOTES:

1.Material:

1.1 Housing: PBT+30%GF UL94V-0, Color Black

1.2 Shell: Brass

1.3 Contact :Phosphor Bronze

2. FINISH:

2.1 Contact Area: Gold Flash

Solder Area: Tin Plated

Under: Ni Plated

3.MECHANICAL:

3.1 Mating Force:3.57kgf Max.

3.2 Unmating Force:1.02kgf Min

3.3 Durability:1500 cycles Min

4.ELECTRICAL:

4.1 Current Rating:1.5A

⑩ 4.2 Dielectric Strength:1KV AC FOR 1 MINUTE

4.3 Contact Resistance:30mΩ Max

4.4 Insulation Resistance:1000 MΩ Min

5.Operating temperature: -55°C TO +85°C

6.PACKIING: Tray

RoHS compliant

Unit: mm