







RECOMMENDED P.C.B LAYOUT

NOTES:

1.Material:

- 1.1 Housing: PBT+30%GF UL94V-0, Color White
- 1.2 Shell: Copper Alloy+
- 1.3 Contact :Brass

2. FINISH:

- 2.1 Contact Area: Selective Gold Flash
- Solder Area: Tin Plated
- Under: Ni Plated

3.MECHANICAL:

- 3.1 Mating Force:3.57kgf Max.
- 3.2 Unmating Force:1.02kgf Min
- 3.3 Durability:1500 cycles Min

4.ELECTRICAL:

- 4.1 Current Rating:1.5A
- 4.2 Dielectric Strength:500V AC FOR 1 MINUTE
- 4.3 Contact Resistance:30mΩ Max
- 4.4 Insulation Resistance:1000 MΩ Min

5.Operating temperature: -55°C TO +85°C

6.PACKIING: Tray

RoHS compliant

Unit: mm