


Wire to Board Connectors

Features:

- 0.079" (2.00mm) contact spacing
- For use with PC board thickness: 0.047" (1.2mm) ~ 0.062" (1.6mm)
- Low profile insulator body, 0.185" (4.7mm) width 0.240" (6.10mm) Height
- Contact termination options include: P.C. tail, surface mount
- Top entry or side entry configurations
- Board retention contacts available
- Designed for high-density connection of internal wires to PCB




Specifications:


Insulator Material	PA66, UL94V-0, Natural Color	
Contact Material	Brass (For Male Header)	Phosphor Bronze (For Female Contact)
Contact Plating	Tin Plating (For Male Header)	Tin Plating, Copper Underplating (For Female Contact)
Current Rating	2 amps	
Voltage Rating	100 V	
Contact Resistance	Initial: 10 milliohms maximum	
Dielectric Withstanding Voltage	800 V AC rms	
Insulation Resistance	1000 megaohms minimum	
Operating Temperature	-40°C to +105°C	
Applicable Wire	AWG #30~#24	

Through-Hole Type Header:


TOP ENTRY




CAVITY NO.




3P~16P



2P





SIDE ENTRY



No.of Circuits	Top Entry	Side Entry		
	EDAC P/N	EDAC P/N	Dim A	Dim B
2	140-502-415-001	140-502-415-000	2.00	6.00
3	140-503-415-001	140-503-415-000	4.00	8.00
4	140-504-415-001	140-504-415-000	6.00	10.00
5	140-505-415-001	140-505-415-000	8.00	12.00
6	140-506-415-001	140-506-415-000	10.00	14.00
7	140-507-415-001	140-507-415-000	12.00	16.00
8	140-508-415-001	140-508-415-000	14.00	18.00
9	140-509-415-001	140-509-415-000	16.00	20.00
10	140-510-415-001	140-510-415-000	18.00	22.00
11	140-511-415-001	140-511-415-000	20.00	24.00
12	140-512-415-001	140-512-415-000	22.00	26.00

Through-Hole Header:






Through-Hole Header:

No.of Circuits	Top Entry	Side Entry		
	EDAC P/N	EDAC P/N	Dim A	Dim B
2	140-502-415-101	140-502-415-100	2.00	6.00
3	140-503-415-101	140-503-415-100	4.00	8.00
4	140-504-415-101	140-504-415-100	6.00	10.00
5	140-505-415-101	140-505-415-100	8.00	12.00
6	140-506-415-101	140-506-415-100	10.00	14.00
7	140-507-415-101	140-507-415-100	12.00	16.00
8	140-508-415-101	140-508-415-100	14.00	18.00
9	140-509-415-101	140-509-415-100	16.00	20.00
10	140-510-415-101	140-510-415-100	18.00	22.00
11	140-511-415-101	140-511-415-100	20.00	24.00
12	140-512-415-101	140-512-415-100	22.00	26.00


SMT Header:

TOP ENTRY




SMT Header:

SIDE ENTRY



No. of Circuits	Top Entry	Side Entry		
	EDAC P/N	EDAC P/N	Dim A (mm)	Dim B (mm)
2	140-502-417-011	140-502-417-060	2.0	8.0
3	140-503-417-011	140-503-417-060	4.0	10.0
4	140-504-417-011	140-504-417-060	6.0	12.0
5	140-505-417-011	140-505-417-060	8.0	14.0
6	140-506-417-011	140-506-417-060	10.0	16.0
7	140-507-417-011	140-507-417-060	12.0	18.0
8	140-508-417-011	140-508-417-060	14.0	20.0
9	140-509-417-011	140-509-417-060	16.0	22.0
10	140-510-417-011	140-510-417-060	18.0	24.0
11	140-511-417-011	140-511-417-060	20.0	26.0
12	140-512-417-011	140-512-417-060	22.0	28.0
13	140-513-417-011	140-513-417-060	24.0	30.0
14	140-514-417-011	140-514-417-060	26.0	32.0
15	140-515-417-011	140-515-417-060	28.0	34.0
16	140-516-417-011	N/A	30.0	36.0

Socket Housing:




Technical drawings of the socket housing showing top, side, and front views with dimensions:

- Top view: Pitch 2.00 ± 0.10 , Overall width $A \pm 0.20$.
- Front view: Pitch $B \pm 0.25$, Overall height 6.85 ± 0.25 , Label "Circuit 1".
- Side view: Overall width 4.40 ± 0.25 , Base width 3.40 ± 0.20 .

No.of Circuits	EDAC P/N			Dim A (mm)	Dim B (mm)
2	140-502-210-011			2.00	5.80
3	140-503-210-011			4.00	7.80
4	140-504-210-011			6.00	9.80
5	140-505-210-011			8.00	11.80
6	140-506-210-011			10.00	13.80
7	140-507-210-011			12.00	15.80
8	140-508-210-011			14.00	17.80
9	140-509-210-011			16.00	19.80
10	140-510-210-011			18.00	21.80
11	140-511-210-011			20.00	23.80
12	140-512-210-011			22.00	25.80
13	140-513-210-011			24.00	27.80
14	140-514-210-011			26.00	29.80
15	140-515-210-011			28.00	31.80
16	140-516-210-011			30.00	33.80


Contact:



EDAC P/N	Wire Range	Insulation O.D	Material
140-941-290	24-30AWG	1.50 MAX.	Phosphor Bronze


PCB Layout:

Through hole top entry




Recommended PCB Layout
PCB Thickness: 1.20~1.60mm
Tolerance: ± 0.05

Through hole side entry




Recommended PCB Layout
PCB Thickness: 1.20~1.60mm
Tolerance: ± 0.05

SMT top entry



Recommended PCB Layout
PCB Thickness: 1.20~1.60mm
Tolerance: ± 0.05

SMT side entry



Recommended PCB Layout
PCB Thickness: 1.20~1.60mm
Tolerance: ± 0.05

TOLERANCE
UNLESS OTHERWISE
SPECIFIED

.X	±0.3
.XX	±0.20
.XXX	±0.100

THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER

ORIGINAL

1

NOTE:

NO COPPER WIRE OR DEFORMATION AFTER STAMPING



MATERIAL: PHOSPHOR BRONZE C5191, HARDNESS 190-210HV

WIRE SIZE: AWG 22-30, OD: 1.50 MAX





PLATING: TIN FLASH OVER NICKEL (NICKEL 30U" MIN, TIN FLASH 80U" MIN)

PACKAGING: 10K PCS/REEL, 100K PCS/BOX. BOX SIZE: 46X46X26 CM

WIRE RANGE	INSULATION O.D.	MATERIAL	FINISH	QTY/REEL
AWG#24-30	1.50mm (max)	PHOSPHOR BRONZE		10,000pcs



WIRE OPENING
UPWARD



MEASURING
POINT (BACK)



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

2.0mm CRIMP STYLE CONNECTOR

ACAD REFERENCE NO.: 140-941-290

DRAWN: P.M.

DATE: OCT. 27/2020

CHECKED: C.B.

DATE: OCT. 27/2020

SCALE: N.T.S.

SHEET 1 OF 1

DRAWING NUMBER: 140-941-290

ISSUE

PART NUMBER: 140-941-290

1